



YAV26LTC38FX90, Compression Terminal, 2/0 Flex G,H,I,K,M, DLO, 2/0 AWG, Cu, 1- Hole, 3/8" Stud, Standard Barrel, 90 Degree

By Burndy

Catalog # [YAV26LTC38FX90](#)

2/0 Flex G,H,I,K,M,DLO, 2/0 AWG, CU, 1 Hole, 3/8 Stud, Standard
Barrel, Inspection Window, 90 Degree

Features

- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding
- For applications greater than 2000 Volts consult cable manufacturer for voltage stress relief instructions

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Yes
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Wire Size	2/0 AWG
Conductor - Copper Flex K Size	2/0 AWG
Range	
Conductor - Copper Flex K Size	"2/0 AWG"
Conductor - Copper Flex M Size	"2/0 AWG"
Conductor - Copper Str Size	"2/0 AWG"
Conductor - Copper Flex I Size	2/0 AWG
Range	
Conductor - Copper Flex G Size	"2/0 AWG"
Conductor - Copper DLO Size	2/0 AWG
Range	
Conductor - Copper Str	"2/0 AWG"
Compact Size	
Conductor - Copper DLO Size	2/0 AWG
Conductor Size	2/0 AWG
Conductor - Copper Flex H Size	"2/0 AWG"
Conductor - Copper Flex G Size	2/0 AWG
Range	



Conductor - Copper Str Navy Size Range 125 (61) Navy

Conductor - Copper Str Navy Size 125

Conductor - CopperWeld Str Size

- 2/0 F AWG
- 2/0 G AWG
- 2/0 J AWG
- 2/0 K AWG
- 2/0 V AWG

Conductor Type CODE/FLEX

Conductor - Copper Str Size Range 2/0 AWG

Conductor - Copper Flex H Size Range 2/0 AWG

Conductor - Copper Flex I Size "2/0 AWG"

Configuration

Physical Attribute - Number of Holes 1

Number of Pad Holes 1

Connector Type STANDARD BARREL

Current

Voltage Rating 35 kV

Voltage - Maximum 35000

Dimensions

Dimension - Pad Width inch	0.93 in
Package Height	0.000 in
Dimension - Height mm	0 mm
Dimension - Hole Size fraction	3/8
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	32 mm
Dimension - Outside Diameter inch	0.63 in
Dimension - Hole Size mm	10.4 mm
Dimension - Hole Size inch	0.41
Dimension - Strip Length inch	13/16
Dimension - Stud Size inch	3/8
Dimension - Stud Size fraction	3/8
Dimension - Bolt Hole Size inch	0.40 in

Dimension - Bolt Size fraction	3/8	Color Code	Black
Physical Attribute - Tongue Angle	90 Degree	Sub Brand	HYLUG
Angle - Pad	90 °	UPC	781810022665
Dimension - Z inch	0.42 in	Type	Standard Barrel, Tin Plated
Dimension - B Length inch	0.81 in	Material	Copper
Dimension - N inch	0.41 in	Plating Type	Tin
Dimension - Bolt Size inch	0.38	Finish Type	Tin-Plated
Dimension - Length Overall inch	1.26 in	UPC 12 Digit	781810022665
		UPC 14 Digit GTIN	00781810022665
General		Logistics	
Trade Name	HYLUG™	Minimum Pack Quantity	1
Die Index	13	Pallet Quantity	24000
Feature - Barrel Type	Standard	Carton Quantity	25
Feature - Barrel Style	Chamfered		
Plated	Yes	Product Assets	
		Catalog [English]	



A Hubbell brand