



YAV26RS3, Uninsulated Right Angle Ring Terminal For 2/0 AWG, 1-Hole, 1/2" Stud

By Burndy
Catalog # [YAV26RS3](#)

Uninsulated Right Angle Ring Terminal For 2/0 AWG



Features

- Manufactured from seamless pure electrolytic copper tubing to provide maximum conductivity, low resistance and excellent ductility for crimping
- Seamless tubular crimp barrel design - No seams to split resulting in a very high quality electrical connection, also can be used on solid conductor
- Double thick tongue structurally a very strong terminal tongue
- Produced from tubular copper, extra copper material assures the compression connector will operate cooler than the conductors it connects
- Internally bevelled barrel for easy cable entry, especially for flexible conductors
- Inspection hole provides easy visual check for proper conductor insertion
- Electro-tin plated for a long lasting durable corrosion resistance

Application

For Use On Copper Commercial (Code) Cable, Type AN Aircraft Cable And Extra Flexible Conductors

Specifications

Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	No
UL Listed	Yes

Conductor

Conductor - Copper Str Size	2/0
Conductor - Copper Str Aircraft Size	AN-2/0
Conductor Size	2/0 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Ring Terminal

Dimensions

Dimension - Outside Diameter inch	0.65 in
Dimension - L Length Overall mm	40 mm
Dimension - Pad Width inch	0.92 in
Dimension - G inch	1.44 in
Dimension - Hole Size mm	13 mm
Dimension - Strip Length inch	13/16
Dimension - Stud Size inch	1/2
Dimension - B Length fraction	13/16 in
Dimension - B Length inch	0.81 in
Dimension - Z inch	0.47 in
Physical Attribute - Tongue Angle	90 Degree
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - Length Overall inch	1.58 in
Dimension - N inch	0.39 in

General

Die Index	44
Trade Name	HYLUG™
Sub Brand	HYLUG
Physical Attribute - Tongue Type	Ring
Plated	Y
Feature - Barrel Type	Standard
Feature - Barrel Style	Chamfered
Type	Ring Tongue
UPC 14 Digit GTIN	00781810025888
Material	Copper
Plating Type	Tin
UPC	781810025888

Logistics

Minimum Pack Quantity	100
Carton Quantity	100
Pallet Quantity	22200



A Hubbell brand