



YAV27L20, Uninsulated Ring Terminal For 3/0 AWG, 1-Hole, 5/16" Stud

By Burndy
Catalog # [YAV27L20](#)

Copper Compression Lug, Ring Tongue, 1 Hole w/ Inspection Hole, AN-3/0, 5/16" Stud, Short Barrel, Tin Plated



Features

- Manufactured from seamless pure electrolytic copper tubing to provide maximum conductivity, low resistance and excellent ductility for crimping
- Seamless tubular crimp barrel design - No seams to split resulting in a very high quality electrical connection, also can be used on solid conductor
- Double thick tongue structurally a very strong terminal tongue
- Produced from tubular copper, extra copper material assures the compression connector will operate cooler than the conductors it connects
- Internally bevelled barrel for easy cable entry, especially for flexible conductors
- Inspection hole provides easy visual check for proper conductor insertion
- Electro-tin plated for a long lasting durable corrosion resistance

Application

Industrials, Hospitals, Utilities, Marine, Computer

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
Industry Standard(s)	• UL467 • Military Specified (Mil-Spec)
Certification - CSA Approved	Yes
UL Listed	Yes

Conductor

Conductor - Copper Str Aircraft Size	AN-3/0
Conductor Size	3/0 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size

Configuration

Physical Attribute - Number of Holes	1
--------------------------------------	---

Connector Type

Ring Terminal

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length fraction	3/4 in
Package Weight	0.000 lb.
Dimension - B Length inch	0.78 in
Dimension - Z inch	0.52 in
Dimension - Pad Width inch	1.03 in
Physical Attribute - Tongue Angle	Straight
Package Height	0.000 in
Dimension - Bolt Hole Size inch	0.33 in
Dimension - Bolt Size fraction	5/16
Dimension - Hole Size mm	8 mm
Dimension - Stud Size inch	5/16 in
Dimension - Length Overall inch	2.45 in
Dimension - N inch	0.52 in

General

Die Index	45
Physical Attribute - Tongue Type	Ring
Trade Name	HYLUG™
Material Composition	• DLP Copper • Tin Plating
Application - For Use On	Copper Commercial (Code) Cable, Type AN Aircraft Cable, Extra Flexible Conductors
Plated	Y
Feature - Barrel Type	Standard
Feature - Barrel Style	Chamfered
Type	Ring Tongue
UPC 14 Digit GTIN	00781810129845
Military Specification	AS20659
Material	Copper
Plating Type	Tin
UPC	781810129845

Logistics

Minimum Pack Quantity	1
Carton Quantity	200
Pallet Quantity	19200



A Hubbell brand