



YAV27LTC14FX, Compression Terminal, 3/0 Flex G,H,I,K,M, DLO, 3/0 AWG, Cu, 1-Hole, 1/4" Stud, Standard Barrel

By Burndy
Catalog # [YAV27LTC14FX](#)

3/0 Flex G,H,I,K,M,DLO, 3/0 AWG, CU, 1 Hole, 1/4 Stud, Standard Barrel, Inspection WIndow

Features

- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding
- For applications greater than 2000 Volts consult cable manufacturer for voltage stress relief instructions

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Wire Size	3/0 AWG
Conductor - Copper Flex K Size Range	3/0 AWG
Conductor - Copper Flex K Size	"3/0 AWG"
Conductor - Copper Flex M Size	"3/0 AWG"
Conductor - Copper Str Size	"3/0 AWG"
Conductor - Copper Flex I Size Range	3/0 AWG
Conductor - Copper Flex G Size	"3/0 AWG"
Conductor - Copper DLO Size Range	3/0 AWG
Conductor - Copper Str Compact Size	"3/0 AWG"
Conductor - Copper DLO Size	3/0 AWG
Conductor Size	3/0 AWG
Conductor - Copper Flex H Size	"3/0 AWG"
Conductor - Copper Flex G Size Range	3/0 AWG
Conductor - Copper Str Navy Size	150



Conductor - CopperWeld Str Size

- 3/0 E AWG
- 3/0 EK AWG
- 3/0 F AWG
- 3/0 G AWG
- 3/0 J AWG
- 3/0 V AWG

Conductor Type
Conductor - Copper Str Size

CODE/FLEX
3/0 AWG

Conductor - Copper Flex H Size Range

3/0 AWG

Conductor - Copper Flex I Size

"3/0 AWG"

Configuration

Physical Attribute - Number of Holes	1
Number of Pad Holes	1
Connector Type	STANDARD BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	1.03 in
Package Height	0.000 in
Dimension - Height mm	0 mm
Dimension - Hole Size fraction	1/4
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	55 mm
Dimension - Outside Diameter inch	0.70 in
Dimension - Hole Size mm	6.9 mm
Dimension - Hole Size inch	0.27
Dimension - Strip Length inch	1 in
Dimension - Stud Size inch	1/4
Dimension - Stud Size fraction	1/4
Dimension - Bolt Hole Size inch	0.27 in
Dimension - Bolt Size fraction	1/4
Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	1 in

Dimension - Z inch	0.33 in	Material	Copper
Dimension - B Length inch	1.00 in	Plating Type	Tin - Electro Plated
Dimension - N inch	0.31 in	Finish Type	Tin-Plated
Dimension - Bolt Size inch	0.25	UPC 12 Digit	781810022481
Dimension - Length Overall inch	2.15 in	UPC 14 Digit GTIN	00781810022481
General		Logistics	
Trade Name	HYLUG™	Minimum Pack Quantity	100
Die Index	14	Pallet Quantity	19600
Feature - Barrel Type	Standard	Carton Quantity	100
Feature - Barrel Style	Chamfered	Product Assets	
Plated	Y	Catalog [English]	
Color Code	Orange	Installation Manual [English]	
UPC	781810022481	Installation Manual [English]	
Type	Standard Barrel, Tin Plated		



A Hubbell brand