



YAV27LTC38FX90, Compression Terminal, 3/0 Flex G,H,I,K,M, DLO, 3/0 AWG, Cu, 1-Hole, 3/8" Stud, Standard Barrel, 90 Degree

By Burndy

Catalog # [YAV27LTC38FX90](#)

3/0 Flex G,H,I,K,M,DLO, 3/0 AWG, CU, 1 Hole, 3/8 Stud, Standard Barrel, Inspection Window, 90 Degree

Features

- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding
- For applications greater than 2000 Volts consult cable manufacturer for voltage stress relief instructions

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Wire Size	3/0 AWG
Conductor - Copper Flex K Size	3/0 AWG
Range	
Conductor - Copper Flex K Size	"3/0 AWG"
Conductor - Copper Flex M Size	"3/0 AWG"
Conductor - Copper Str Size	"3/0 AWG"
Conductor - Copper Flex I Size	3/0 AWG
Range	
Conductor - Copper Flex G Size	"3/0 AWG"
Conductor - Copper DLO Size	3/0 AWG
Range	
Conductor - Copper Str	"3/0 AWG"
Compact Size	
Conductor - Copper DLO Size	3/0 AWG
Conductor Size	3/0 AWG
Conductor - Copper Flex H Size	"3/0 AWG"
Conductor - Copper Flex G Size	3/0 AWG
Range	
Conductor - Copper Str Navy	150
Size	



Conductor - CopperWeld Str Size	• 3/0 E AWG • 3/0 EK AWG • 3/0 F AWG • 3/0 G AWG • 3/0 J AWG • 3/0 V AWG
---------------------------------	--

Conductor Type	CODE/FLEX
Conductor - Copper Str Size	3/0 AWG
Range	
Conductor - Copper Flex H Size	3/0 AWG
Range	
Conductor - Copper Flex I Size	"3/0 AWG"

Configuration

Physical Attribute - Number of Holes	1
Number of Pad Holes	1
Connector Type	STANDARD BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	1.03 in
Package Height	0.000 in
Dimension - Height mm	0 mm
Dimension - Hole Size fraction	3/8
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	33 mm
Dimension - Outside Diameter inch	0.70 in
Dimension - Hole Size mm	10.4 mm
Dimension - Hole Size inch	0.41
Dimension - Strip Length inch	1 in
Dimension - Stud Size fraction	3/8
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Physical Attribute - Tongue Angle	90 Degree
Angle - Pad	90 °

Dimension - B Length fraction	1 in	UPC	781810129319
Dimension - Z inch	0.42 in	Type	Standard Barrel, Tin Plated
Dimension - B Length inch	1.00 in	Material	Copper
Dimension - N inch	0.41 in	Plating Type	Tin
Dimension - Bolt Size inch	0.38	Finish Type	Tin-Plated
Dimension - Length Overall	1.29 in	UPC 12 Digit	781810129319
inch		UPC 14 Digit GTIN	00781810129319

General

Trade Name	HYLUG™
Die Index	14
Feature - Barrel Type	Standard
Feature - Barrel Style	Chamfered
Plated	Y
Color Code	Orange

Logistics

Minimum Pack Quantity	1
Pallet Quantity	19200
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)



A Hubbell brand