



YAV2CL2NT10FX, Compression Terminal, 2 Flex G, H, I, K, M, DLO, 2 AWG, Cu, 2-Hole, #10 Stud, 5/8" Spacing, Narrow Tongue

By Burndy
Catalog # [YAV2CL2NT10FX](#)

2 Flex G,H,I,K,M,DLO, 2 AWG, CU, 2 Hole, #10 Stud, 5/8 IN Spacing, Standard Barrel, Inspection WIndow, Narrow Tongue

Features

- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding
- For applications greater than 2000 Volts consult cable manufacturer for voltage stress relief instructions

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Wire Size	2 AWG
Conductor - Copper Flex K Size Range	2 AWG
Conductor - Copper Flex K Size	"2 AWG"
Conductor - Copper Flex M Size	"2 AWG"
Conductor - Copper Str Size	"2 AWG"
Conductor - Copper Flex I Size Range	2 AWG
Conductor - Copper Flex G Size	"2 AWG"
Conductor - Copper DLO Size Range	2 AWG
Conductor - Copper Str Compact Size	"2 AWG"
Conductor - Copper DLO Size	2 AWG
Conductor Size	2 AWG
Conductor - Copper Flex H Size	"2 AWG"
Conductor - Copper Flex G Size Range	2 AWG

Conductor - Copper Str Navy Size Range 60 (37) Navy

Conductor - Copper Str Navy Size 60

Conductor - Copper Solid Size 2 AWG

- Conductor - CopperWeld Str Size
- 2 A AWG
 - 2 F AWG
 - 2 G AWG
 - 2 J AWG
 - 2 K AWG
 - 2 N AWG
 - 2 P AWG

Conductor Type CODE/FLEX

Conductor - Copper Str Size Range 2 AWG

Conductor - Copper Flex H Size Range 2 AWG

Conductor - Copper Flex I Size "2 AWG"

Configuration

Physical Attribute - Number of Holes	2
Number of Pad Holes	2
Connector Type	STANDARD BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	0.48 in
Package Height	0.000 in
Dimension - Hole Size fraction	#10
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	54 mm
Dimension - Outside Diameter inch	0.46 in
Dimension - Hole Size mm	5.3 mm
Dimension - Hole Size inch	0.21
Dimension - Strip Length inch	11/16
Dimension - Stud Size inch	#10
Dimension - Stud Size fraction	#10



Dimension - Bolt Hole Size inch 0.20 in
Dimension - Bolt Size fraction #8-#10
Physical Attribute - Tongue Straight
Angle
Dimension - B Length fraction 5/8 in
Dimension - Z inch 0.27 in
Dimension - B Length inch 0.63 in
Dimension - N inch 0.25 in
Dimension - Bolt Size inch 0.21
Dimension - Length Overall 2.14 in
inch

General

Trade Name HYLUG™
Die Index 10
Feature - Barrel Type Standard
Feature - Barrel Style Chamfered
Plated Y

Color Code Brown
Sub Brand TERMINALS, HYLUG
UPC 781810038581
Type YAV-L-NTFX
Material Copper
Plating Type Tin - Electro Plated
Finish Type Tin-Plated
UPC 14 Digit GTIN 00781810038581

Logistics

Minimum Pack Quantity 1
Pallet Quantity 76800
Carton Quantity 100

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[English\]](#)
[Installation Manual \[English\]](#)



A Hubbell brand