



YAV2CL2NT10FX90, Cu Compression, 2-Hole, #10 Stud, 5/8" Spacing, Narrow Tongue, Standard Barrel, 90 Degree, 2 Flex

By Burndy
Catalog # [YAV2CL2NT10FX90](#)

2 Flex G,H,I,K,M,DLO, 2 AWG, CU, 2 Hole, #10 Stud, 5/8 IN Spacing, Standard Barrel, Inspection WIndow, Narrow Tongue, 90 Degree

Features

- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding
- For applications greater than 2000 Volts consult cable manufacturer for voltage stress relief instructions

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	TAA Compliant (All status valid till December 2026)
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Wire Size	2 AWG
Conductor - Copper Flex K Size Range	2 AWG
Conductor - Copper Flex K Size	"2 AWG"
Conductor - Copper Flex M Size	"2 AWG"
Conductor - Copper Str Size	"2 AWG"
Conductor - Copper Flex I Size Range	2 AWG
Conductor - Copper Flex G Size	"2 AWG"
Conductor - Copper DLO Size Range	2 AWG
Conductor - Copper Str Compact Size	"2 AWG"
Conductor - Copper DLO Size	2 AWG
Conductor Size	2 AWG
Conductor - Copper Flex H Size	"2 AWG"



Conductor - Copper Flex G Size Range	2 AWG
Conductor - Copper Str Navy Size Range	60 (37) Navy
Conductor - Copper Str Navy Size	60
Conductor - Copper Solid Size	2 AWG
Conductor - CopperWeld Str Size	• 2 A AWG • 2 F AWG • 2 G AWG • 2 J AWG • 2 K AWG • 2 N AWG • 2 P AWG
Conductor Type	CODE/FLEX
Conductor - Copper Str Size Range	2 AWG
Conductor - Copper Flex H Size Range	2 AWG
Conductor - Copper Flex I Size	"2 AWG"

Configuration

Physical Attribute - Number of Holes	2
Number of Pad Holes	2
Connector Type	STANDARD BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	0.48 in
Package Height	0.000 in
Dimension - Height mm	29.2 mm
Dimension - Hole Size fraction	#10
Dimension - Height inch	1.15 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	38 mm
Dimension - Outside Diameter inch	0.46 in

Dimension - Hole Size mm	5.3 mm	Feature - Barrel Type	Standard
Dimension - Hole Size inch	0.21	Feature - Barrel Style	Chamfered
Dimension - Strip Length inch	11/16	Plated	Y
Dimension - Stud Size fraction	#10	Color Code	Brown
Dimension - Bolt Hole Size inch	0.20 in	Sub Brand	HYLUG
Dimension - Bolt Size fraction	#8-#10	UPC	781810376201
Physical Attribute - Tongue	90 Degree	Type	Standard Barrel, Tin Plated
Angle		Material	Copper
Angle - Pad	90 °	Plating Type	Tin - Electro Plated
Dimension - B Length fraction	5/8 in	Finish Type	Tin-Plated
Dimension - Z inch	0.27 in	UPC 12 Digit	781810376201
Dimension - B Length inch	0.63 in	UPC 14 Digit GTIN	00781810376201
Dimension - N inch	0.25 in		
Dimension - Bolt Size inch	0.21		
Dimension - Length Overall	1.48 in		
inch			
General		Logistics	
Trade Name	HYLUG™	Minimum Pack Quantity	1
Die Index	10	Pallet Quantity	46400
		Carton Quantity	100
		Product Assets	
		Catalog [English]	



A Hubbell brand