



YAV2CL2NT14FX, Cu Compression, 2-Hole, 1/4" Stud, 5/8" Spacing, Narrow Tongue, Standard Barrel, 2 Flex

By Burndy
Catalog # [YAV2CL2NT14FX](#)



2 Flex G,H,I,K,M,DLO, 2 AWG, CU, 2 Hole, 1/4 Stud, 5/8 IN Spacing, Standard Barrel, Inspection WIndow, Narrow Tongue

Features

- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding
- For applications greater than 2000 Volts consult cable manufacturer for voltage stress relief instructions

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	BABA Compliant (All status valid till December 2026)
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Wire Size	2 AWG
Conductor - Copper Flex K Size Range	2 AWG
Conductor - Copper Flex K Size	"2 AWG"
Conductor - Copper Flex M Size	"2 AWG"
Conductor - Copper Str Size	"2 AWG"
Conductor - Copper Flex I Size Range	2 AWG
Conductor - Copper Flex G Size	"2 AWG"
Conductor - Copper DLO Size Range	2 AWG
Conductor - Copper Str Compact Size	"2 AWG"
Conductor - Copper DLO Size	2 AWG
Conductor Size	2 AWG
Conductor - Copper Flex H Size	"2 AWG"

Conductor - Copper Flex G Size Range	2 AWG
Conductor - Copper Str Navy Size Range	60 (37) Navy
Conductor - Copper Str Navy Size	60
Conductor - Copper Solid Size	2 AWG
Conductor - CopperWeld Str Size	• 2 A AWG • 2 F AWG • 2 G AWG • 2 J AWG • 2 K AWG • 2 N AWG • 2 P AWG
Conductor Type	CODE/FLEX
Conductor - Copper Str Size Range	2 AWG
Conductor - Copper Flex H Size Range	2 AWG
Conductor - Copper Flex I Size	"2 AWG"

Configuration

Physical Attribute - Number of Holes	2
Number of Pad Holes	2
Connector Type	STANDARD BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	0.48 in
Package Height	0.000 in
Dimension - Hole Size fraction	1/4
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	57 mm
Dimension - Outside Diameter inch	0.46 in
Dimension - Hole Size mm	6.9 mm
Dimension - Hole Size inch	0.27
Dimension - Strip Length inch	11/16

Dimension - Stud Size inch	1/4	Plated	Y
Dimension - Stud Size fraction	1/4	Color Code	Brown
Dimension - Bolt Hole Size inch	0.27 in	Sub Brand	HYLUG
Dimension - Bolt Size fraction	1/4	UPC	781810274217
Physical Attribute - Tongue Angle	Straight	Type	YAV-L-NTFX, Standard Barrel Narrow Tongue
Dimension - B Length fraction	5/8 in	Material	Copper
Dimension - Z inch	0.34 in	Plating Type	Tin - Electro Plated
Dimension - B Length inch	0.63 in	Finish Type	Tin-Plated
Dimension - N inch	0.31 in	UPC 14 Digit GTIN	00781810274217
Dimension - Bolt Size inch	0.25		
Dimension - Length Overall inch	2.26 in		
General		Logistics	
Trade Name	HYLUG™	Minimum Pack Quantity	1
Die Index	10	Carton Quantity	50
Feature - Barrel Type	Standard		
Feature - Barrel Style	Chamfered		

Trade Name	HYLUG™
Die Index	10
Feature - Barrel Type	Standard
Feature - Barrel Style	Chamfered

- [Catalog \[English\]](#)
- [Installation Manual \[English\]](#)
- [Installation Manual \[English\]](#)



A Hubbell brand