



YAV2CL3NK, Compression Terminal, 2 Flex G,H,I,K,M, DLO, 2 AWG Cu, 1-Hole, #10 Stud, Standard Barrel, Nickel Plated

By Burndy

Catalog # [YAV2CL3NK](#)

Copper Compression Terminal

Features

- Seamless, heavy duty uninsulated compression terminal provides a strong connector for demanding applications requiring high reliability
- Suitable for use on Type AN aircraft cable, extra flexible conductors and commercial (code) conductors

Application

Wire Termination

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Flex G Size	"2 AWG"
Conductor - Copper Str	"2 AWG"
Compact Size	
Conductor - Copper DLO Size	2 AWG
Conductor Size	2 AWG
Conductor - Copper Flex H Size	"2 AWG"
Conductor - Copper Str Navy Size	60
Conductor - Copper Str Aircraft Size	AN 2
Conductor - Material	COPPER
Wire Size	2 AWG
Conductor - Copper Flex K Size	"2 AWG"
Conductor - Copper Flex M Size	"2 AWG"
Conductor Type	CODE/FLEX
Conductor - Copper Str Size	"2 AWG"
Conductor - Copper Flex I Size	"2 AWG"

Configuration

Physical Attribute - Number of Holes	1
Number of Pad Holes	1
Connector Type	STANDARD BARREL



Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	0.69 in
Dimension - Bolt Hole Size inch	0.20 in
Package Height	0.000 in
Dimension - Hole Size fraction	#10
Dimension - Bolt Size fraction	#8-#10
Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	5/8 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Z inch	0.35 in
Dimension - L Length Overall mm	44 mm
Dimension - B Length inch	0.60 in
Dimension - Outside Diameter inch	0.46 in
Dimension - D inch	0.69 in
Dimension - N inch	0.34 in
Dimension - Hole Size mm	5.3 mm
Dimension - Bolt Size inch	0.21
Dimension - Hole Size inch	0.21
Dimension - Length Overall inch	1.72 in
Dimension - Strip Length inch	5/8
Dimension - Stud Size fraction	#10

General

Feature - Barrel Type	Standard
Feature - Barrel Style	Chamfered
Plated	Y
Trade Name	HYLUG™
Die Index	10
UPC	781810069837
Type	Standard Barrel, Nickel Plated
Material	Copper
Plating Type	Nickel
Finish Type	Nickel Plated
UPC 12 Digit	781810069837
UPC 14 Digit GTIN	00781810069837

Logistics

Minimum Pack Quantity	200
Pallet Quantity	29400

Carton Quantity200

Product Assets

[Catalog \[English\]](#)



A Hubbell brand