



YAV2CL4TC14FXG1, Compression Terminal,
2 Flex G,H,I,K,M, DLO, 2 AWG Cu, 4-Hole,
Split Pad, 1/4" Stud, Standard Barrel

By Burndy
Catalog # [YAV2CL4TC14FXG1](#)

Copper Compression Terminal

Features

- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding
- For applications greater than 2000 Volts consult cable manufacturer for voltage stress relief instructions

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Material	COPPER
Wire Size	2 AWG
Conductor - Copper Flex K Size Range	2 AWG
Conductor - Copper Flex K Size	"2 AWG"
Conductor - Copper Flex M Size	"2 AWG"
Conductor - Copper Str Size	"2 AWG"
Conductor - Copper Flex I Size Range	2 AWG
Conductor - Copper Flex G Size	"2 AWG"
Conductor - Copper DLO Size Range	2 AWG
Conductor - Copper Str Compact Size	"2 AWG"
Conductor - Copper DLO Size	2 AWG
Conductor Size	2 AWG
Conductor - Copper Flex H Size	"2 AWG"
Conductor - Copper Flex G Size Range	2 AWG
Conductor - Copper Str Navy Size Range	60 (37) Navy
Conductor - Copper Str Navy Size	60



Conductor - CopperWeld Str Size	• 2 A AWG • 2 F AWG • 2 G AWG • 2 J AWG • 2 K AWG • 2 N AWG • 2 P AWG
---------------------------------	---

Conductor Type	CODE/FLEX
Conductor - Copper Str Size Range	2 AWG
Conductor - Copper Flex H Size Range	2 AWG
Conductor - Copper Flex I Size	"2 AWG"

Configuration

Physical Attribute - Number of Holes	4
Number of Pad Holes	1
Connector Type	STANDARD BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	1.38 in
Package Height	0.000 in
Dimension - Height mm	0 mm
Dimension - Hole Size fraction	1/4
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - F Width Center to Center inch	0.75 in
Package Width	0.000 in
Dimension - L Length Overall mm	72 mm
Dimension - Outside Diameter inch	0.46 in
Width	1.38 in
Dimension - Hole Size mm	6.9 mm
Dimension - Hole Size inch	0.27
Dimension - Strip Length inch	11/16
Dimension - Stud Size inch	1/4
Dimension - Stud Size fraction	1/4
Dimension - Bolt Hole Size inch	0.27 in
Dimension - Bolt Size fraction	1/4

Length	2.84 in	Plated	Y
Physical Attribute - Tongue	Straight	Color Code	Brown
Angle		UPC	781810411322
Dimension - B Length fraction	5/8 in	Type	Standard Barrel, Tin Plated
Dimension - Z inch	0.83 in	Material	Copper
Dimension - B Length inch	0.62 in	Plating Type	Tin - Electro Plated
Height	0.11 in	Finish Type	Tin-Plated
Dimension - N inch	0.31 in	UPC 12 Digit	781810411322
Dimension - Bolt Size inch	0.25	UPC 14 Digit GTIN	00781810411322
Dimension - Length Overall inch	2.84 in		
Dimensions	2.84 in x 1.38 in x 0.11 in		
General		Logistics	
Trade Name	HYLUG™	Minimum Pack Quantity	20
Die Index	10	Pallet Quantity	15360
Feature - Barrel Type	Standard	Carton Quantity	20
Feature - Barrel Style	Chamfered	Product Assets	
		Catalog [English]	



A Hubbell brand