



BURNDY

[YAV2CLBOX, Uninsulated Ring Terminal, AN-2 Flex, 1-Hole, 3/8" Stud](#)

By Burndy

Catalog # [YAV2CLBOX](#)

Copper Compression Lug, Ring Tongue, 1 Hole w/ Inspection Hole, AN-2 Flex, 3/8" Stud, Short Barrel, Tin Plated, Die index: 41



Features

- Double thick tongue perfect for demanding applications requiring high reliability
- Maximum conductivity, low resistance, excellent ductility
- Seamless tubular crimp barrel - no seams to split
- Extra copper material assure connector operates cooler than the conductor
- Internally bevelled barrel for easy cable entry, especially for flexible conductors

Application

Industrials, Hospitals, Utilities, Marine, Computer

Specifications

Certification - UL Recognized
No
Certification - cULus
No
EU RoHS Indicator
Yes
Industry Standard(s)

- UL467
- Military Specified (Mil-Spec)

Certification - ETL
No
Standards - Industry Standards Met

- UL467
- Military Specified (Mil-Spec)

Standards - RoHS Compliance Status
CM
UL Listed
Yes
Certification - CSA Approved
Yes

Conductor

Conductor - Copper Str Size
2
Conductor - Copper DLO Size
2 (150/#24)
Conductor Size
2 AWG
Conductor - Copper Str Aircraft Size
AN 2
Conductor Type

- CU C Solid-Size
- CU C Str-Size

Conductor - Copper Str Size Range
2 AWG

Configuration

Physical Attribute - Number of Holes
1
Connector Type
Ring Terminal

Dimensions

Dimension - Pad Width inch
0.69 in
Package Height
0.000 in
Package Weight
0.000 lb.
Package Length
0.000 in
Package Width
0.000 in
Dimension - Outside Diameter inch
0.46 in
Dimension - Hole Size mm
10 mm
Dimension - Strip Length inch
5/8 in
Dimension - Stud Size inch
3/8
Dimension - Bolt Hole Size inch
0.39 in
Dimension - Bolt Size fraction
3/8
Physical Attribute - Tongue Angle
Straight
Dimension - B Length fraction
5/8 in

Dimension - Z inch
0.35 in
Dimension - B Length inch
0.53 in
Dimension - N inch
0.34 in
Dimension - Inside Diameter inch
0.36 in
Dimension - Length Overall inch
1.72 in

General

Material Composition

- DLP Copper
- Tin Plating

Trade Name
HYLUG™
Die Index
41
Military Specification
AS20659
Application - For Use On
Copper Commercial (Code) Cable, Type AN Aircraft Cable, Extra Flexible Conductors
Feature - Barrel Style

- Chamfered
- Skived

Plated
Y
Physical Attribute - Tongue Type
Ring
Sub Brand
HYLUG
UPC
781810539682
Type
Ring Tongue
Material
Copper
Plating Type
Tin - Electro Plated
UPC 14 Digit GTIN
00781810539682

Logistics

Carton Quantity
10

Product Assets

[Catalog,\[English\]](#)



A Hubbell brand
© 2026 Hubbell Incorporated. All rights reserved
BRDY_CA-YAV2CLBOX-SPEC-EN | REV 5/2026