



YAV2CLNT14BELL, Compression Terminal, 2 Flex G,H,I,K,M, DLO, 2 AWG Cu, 1-Hole, 1/4" Stud, Standard Barrel

By Burndy

Catalog # [YAV2CLNT14BELL](#)

Copper Compression Terminal

Application

Wire Termination

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Copper Flex G Size	"2 AWG"
Conductor - Copper DLO Size	N/A
Range	
Conductor - Copper Str	"2 AWG"
Compact Size	
Conductor - Copper DLO Size	2 AWG
Conductor Size	2 AWG
Conductor - Copper Flex H Size	"2 AWG"
Conductor - Copper Flex G Size	2 AWG
Range	
Conductor - Copper Str Navy	60
Size	
Conductor - Material	COPPER
Wire Size	2 AWG
Conductor - Copper Flex K Size	2 AWG
Range	
Conductor - Copper Flex K Size	"2 AWG"
Conductor - Copper Flex M Size	"2 AWG"
Conductor Type	CODE/FLEX
Conductor - Copper Str Size	2 AWG
Range	
Conductor - Copper Str Size	"2 AWG"
Conductor - Copper Flex H Size	2 AWG
Range	
Conductor - Copper Flex I Size	"2 AWG"
Conductor - Copper Flex I Size	2 AWG
Range	

Configuration

Physical Attribute - Number of Holes	1
--------------------------------------	---



Connector Type	STANDARD BARREL
----------------	-----------------

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	0.48 in
Dimension - Bolt Hole Size inch	0.27 in
Package Height	0.000 in
Dimension - Height mm	0 mm
Dimension - Hole Size fraction	1/4
Dimension - Bolt Size fraction	1/4
Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	5/8 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Z inch	0.32 in
Dimension - L Length Overall mm	43 mm
Dimension - B Length inch	0.62 in
Dimension - Outside Diameter inch	0.46 in
Dimension - D inch	0.59 in
Dimension - N inch	0.27 in
Dimension - Hole Size mm	6.9 mm
Dimension - Bolt Size inch	0.25
Dimension - Hole Size inch	0.27
Dimension - Length Overall inch	1.71 in
Dimension - Strip Length inch	11/16
Dimension - Stud Size fraction	1/4

General

Feature - Barrel Type	Standard
Feature - Barrel Style	Chamfered
Plated	Y
Color Code	Brown
Trade Name	HYLUG™
Die Index	10
UPC	781810457689
Type	Standard Barrel, Tin Plated
Material	COPPER
Plating Type	Tin - Electro Plated

Finish Type	Tin-Plated	Temperature Rating	194
UPC 12 Digit	781810457689	Product Assets Catalog [English]	
UPC 14 Digit GTIN	00781810457689		

Operational



A Hubbell brand