



YAV2CLTC12FX, Compression Terminal, 2 Flex G,H,I,K,M, DLO, 2 AWG Cu, 1-Hole, 1/2" Stud, Standard Barrel

By Burndy
Catalog # YAV2CLTC12FX

2 Flex G,H,I,K,M,DLO, 2 AWG, CU, 1 Hole, 1/2 Stud, Standard Barrel, Inspection WIndow

Features

- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding
- For applications greater than 2000 Volts consult cable manufacturer for voltage stress relief instructions

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Wire Size	2 AWG
Conductor - Copper Flex K Size Range	2 AWG
Conductor - Copper Flex K Size	"2 AWG"
Conductor - Copper Flex M Size	"2 AWG"
Conductor - Copper Str Size	"2 AWG"
Conductor - Copper Flex I Size Range	2 AWG
Conductor - Copper Flex G Size	"2 AWG"
Conductor - Copper DLO Size Range	2 AWG
Conductor - Copper Str Compact Size	"2 AWG"
Conductor - Copper DLO Size	2 AWG
Conductor Size	2 AWG
Conductor - Copper Flex H Size	"2 AWG"
Conductor - Copper Flex G Size Range	2 AWG



Conductor - Copper Str Navy Size Range	60 (37) Navy
Conductor - Copper Str Navy Size	60
Conductor - Copper Solid Size	2 AWG
Conductor - CopperWeld Str Size	• 2 A AWG • 2 F AWG • 2 G AWG • 2 J AWG • 2 K AWG • 2 N AWG • 2 P AWG

Conductor Type	CODE/FLEX
Conductor - Copper Str Size Range	2 AWG
Conductor - Copper Flex H Size Range	2 AWG
Conductor - Copper Flex I Size	"2 AWG"

Configuration

Physical Attribute - Number of Holes	1
Number of Pad Holes	1
Connector Type	STANDARD BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	0.73 in
Package Height	0.000 in
Dimension - Height mm	0 mm
Dimension - Hole Size fraction	1/2
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	54 mm
Dimension - Outside Diameter inch	0.46 in
Dimension - Hole Size mm	13.5 mm
Dimension - Hole Size inch	0.53
Dimension - Strip Length inch	11/16
Dimension - Stud Size inch	1/2

Dimension - Stud Size fraction	1/2	Physical Attribute - Tongue	Standard
Dimension - Bolt Hole Size inch	0.52 in	Type	
Dimension - Bolt Size fraction	1/2	Sub Brand	HYLUG
Physical Attribute - Tongue	Straight	UPC	781810022795
Angle		Type	Standard Barrel, Tin Plated
Dimension - B Length fraction	5/8 in	Material	Copper
Dimension - Z inch	0.55 in	Plating Type	Tin - Electro Plated
Dimension - B Length inch	0.63 in	Finish Type	Tin-Plated
Dimension - N inch	0.53 in	UPC 12 Digit	781810022795
Dimension - Bolt Size inch	0.5	UPC 14 Digit GTIN	00781810022795
Dimension - Length Overall	2.12 in		
inch			
General		Logistics	
Trade Name	HYLUG™	Minimum Pack Quantity	1
Die Index	10	Pallet Quantity	48000
Feature - Barrel Type	Standard	Carton Quantity	50
Feature - Barrel Style	Chamfered		
Plated	Y	Product Assets	
Color Code	Brown	Catalog [English]	
		Installation Manual [English]	
		Installation Manual [English]	



A Hubbell brand