



YAV2CLTC38FX, Cu Compression, #2 Cu Flex, 1-Hole, 3/8" Stud, Standard Barrel

By Burndy

Catalog # [YAV2CLTC38FX](#)

Copper Compression Lug, 1 Hole w/ Inspection Window, 2 Flex, 3/8" Stud, Short Barrel, Tin Plated



Application

For Flex Conductors

Specifications

Certification - UL Recognized	No
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	Copper
Conductor - Copper Flex K Size Range	2 AWG
Conductor - Copper Flex K Size	2 AWG
Conductor - Copper Flex M Size	2 AWG
Conductor - Copper Str Size	2 AWG
Conductor - Copper Flex I Size Range	2 AWG
Conductor - Copper Flex G Size	2 AWG
Conductor - Copper DLO Size Range	2 AWG
Conductor - Copper DLO Size	• 3 (125/#24) DLO • 2 (150/#24) DLO
Conductor Size	2 AWG
Conductor - Copper Flex H Size	2 AWG
Conductor - Copper Flex G Size Range	2 AWG
Conductor - Copper Str Navy Size	60 (37) Navy
Conductor - Copper Solid Size	2 AWG
Conductor - CopperWeld Str Size	• 2 A AWG • 2 F AWG • 2 G AWG • 2 J AWG • 2 K AWG • 2 N AWG • 2 P AWG
Conductor - Copper Str Size Range	2 AWG
Conductor - Copper Flex H Size Range	2 AWG

Conductor - Copper Flex I Size 2 AWG

Configuration

Physical Attribute - Number of Holes	1
Connector Type	STANDARD BARREL

Current

Voltage - Maximum	35000
-------------------	-------

Dimensions

Dimension - Pad Width inch	0.68 in
Package Height	0.000 in
Dimension - Height mm	0 mm
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	46 mm
Dimension - Outside Diameter inch	0.46 in
Dimension - Hole Size mm	10 mm
Dimension - Hole Size inch	0.40 in
Dimension - Strip Length inch	11/16
Dimension - Stud Size inch	3/8
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	5/8 in
Dimension - Z inch	0.42 in
Dimension - B Length inch	0.63 in
Dimension - N inch	0.41 in
Dimension - Length Overall inch	1.81 in

General

Trade Name	HYLUG™
Die Index	10
Feature - Barrel Type	Standard
Feature - Barrel Style	Chamfered
Plated	Y
Color Code	Brown
Physical Attribute - Tongue Type	Standard

Sub Brand	HYLUG
UPC	781810022443
Type	Standard Barrel, Tin Plated
Material	COPPER
Plating Type	Tin - Electro Plated
UPC 12 Digit	781810022443
UPC 14 Digit GTIN	00781810022443

Logistics

Pallet Quantity	48000
Carton Quantity	50

Product Assets

- [Catalog \[English\]](#)
- [Installation Manual \[English\]](#)
- [Installation Manual \[English\]](#)



A Hubbell brand