



YAV35M10, Compression Terminal

By Burndy
Catalog # [YAV35M10](#)

Copper Compression Terminal



Features

- Barrel is designed with an internal chamfer at the wire entry to ensure smooth insertion of the wire, preventing possible damaging of the strands
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive
- Compatible Standards: IEC61238-1, UL 486A-486B, CSA-C22.2 No. 65-03

Application

Metric Wire Termination

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Material	COPPER
Conductor - Copper Str Size	2 AWG
Conductor - Copper DLO Size Range	N/A
Conductor Size	35 mm ²
Conductor Type	CLASS 2
Conductor - Copper Str Size Range	2 AWG

Configuration

Physical Attribute - Number of Holes	1
Number of Pad Holes	1
Connector Type	METRIC

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	0.68 in
Package Height	0.000 in
Dimension - Hole Size fraction	3/8
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	3 mm
Dimension - Outside Diameter inch	0.44 in
Dimension - Hole Size mm	10.4 mm
Dimension - Hole Size inch	0.41
Dimension - Strip Length inch	0.67 in
Dimension - Stud Size inch	#10
Dimension - Stud Size fraction	3/8
Dimension - Bolt Hole Size inch	0.20 in
Dimension - Bolt Size fraction	3/8
Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	11/16 in
Dimension - Z inch	0.42 in
Dimension - B Length inch	0.46 in
Dimension - D inch	0.84 in
Dimension - N inch	0.39 in
Dimension - Inside Diameter inch	0.31 in
Dimension - Bolt Size inch	0.38
Dimension - Length Overall inch	0.10 in

General

Trade Name	HYLUG™
Die Index	10
Feature - Barrel Style	• Chamfered • Skived
Plated	Y
Color Code	Brown
Sub Brand	Terminals, HYLUG
UPC	781810294185
Type	Metric Terminals
Construction Material - Main Material	Copper tubing
Plating Type	Copper
Finish Type	Tin - Electro Plated
UPC 12 Digit	Tin-Plated
	781810294185

UPC 14 Digit GTIN

00781810294185

Logistics

Minimum Pack Quantity	50
Carton Quantity	50



Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)