



YAV4CL22, Compression Terminal, AN-4, 1-Hole, 3/8" Stud

By Burndy
Catalog # [YAV4CL22](#)

Copper Compression Terminal



Application

Wire Termination

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Copper Flex G Size	"4 AWG"
Conductor - Copper Str	"4 AWG"
Compact Size	
Conductor - Copper DLO Size	4 AWG
Conductor Size	4 AWG
Conductor - Copper Flex H Size	"4 AWG"
Conductor - Copper Str Navy Size	40
Conductor - Copper Solid Size	4
Conductor - Copper Str Aircraft Size Range	AN 4
Conductor - Copper Str Aircraft Size	AN 4
Conductor - Material	COPPER
Wire Size	4 AWG
Conductor - Copper Flex K Size	"4 AWG"
Conductor - Copper Flex M Size	"4 AWG"
Conductor Type	CODE/FLEX
Conductor - Copper Str Size	"4 AWG"
Conductor - Copper Flex I Size	"4 AWG"

Configuration

Physical Attribute - Number of Holes	1
Connector Type	STANDARD BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	0.63 in
Package Height	0.000 in
Dimension - Hole Size fraction	3/8
Dimension - Bolt Size fraction	3/8
Physical Attribute - Tongue Angle	Straight
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Z inch	0.33 in
Dimension - L Length Overall mm	38 mm
Dimension - B Length inch	0.47 in
Dimension - D inch	0.64 in
Dimension - N inch	0.31 in
Dimension - Hole Size mm	10.4 mm
Dimension - Bolt Size inch	0.38
Dimension - Hole Size inch	0.41
Dimension - Length Overall inch	1.48 in
Dimension - Stud Size inch	3/8
Dimension - Stud Size fraction	3/8

General

Feature - Barrel Type	Standard
Feature - Barrel Style	Chamfered
Plated	Y
Trade Name	HYLUG™
Die Index	8
UPC	781810464243
Type	Standard Barrel, Tin Plated
Material	COPPER
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810464243
UPC 14 Digit GTIN	00781810464243

Logistics

Carton Quantity	38
-----------------	----

Product Assets

[Catalog \[English\]](#)