



YAV4CL2NK, Uninsulated Ring Terminal For 4 AWG, 1-Hole, 3/8" Stud, Nickel Plated

By Burndy

Catalog # [YAV4CL2NK](#)

Uninsulated Ring Terminal For 4 AWG (Nickel Plated)



Features

- Nickel plated for high temperature applications up to 650°F continuous service and 750°F intermittent service
- Manufactured from seamless pure electrolytic copper tubing to provide maximum conductivity, low resistance, and excellent ductility for crimping
- Double thick tongue provides a structurally strong terminal tongue
- Produced from tubular copper, extra copper material assures the ompression terminal will operate cooler than the conductors it connects
- Internally beveled barrel for easy cable entry, especially for flexible conductors
- Inspection hole provides easy visual check for proper conductor insertion

Specifications

Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor - Copper Str Size	4
Conductor - Copper Flex K Size	4
Conductor - Copper Flex M Size	4
Conductor - Copper Solid Size	4
Conductor - Copper Str Aircraft Size	AN 4
Conductor - Copper Flex G Size	4
Conductor - Copper Flex H Size	4
Conductor Size	4 AWG
Conductor - Copper Str Size	4 AWG
Range	
Conductor Type	• CU C Solid-Size • CU C Str-Size
Conductor - Copper Flex I Size	4

Configuration

Physical Attribute - Number of Holes	1
Number of Holes	1
Connector Type	Ring Terminal

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - Outside Diameter inch	0.38 in
Dimension - Pad Width inch	0.63 in
Package Height	0.000 in
Dimension - Hole Size mm	10 mm
Dimension - Strip Length inch	1/2
Dimension - Stud Size inch	3/8 in
Dimension - B Length fraction	1/2 in
Dimension - B Length inch	0.47 in
Dimension - Z inch	0.33 in
Physical Attribute - Tongue Angle	Straight
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Dimension - Length Overall inch	1.48 in
Dimension - N inch	0.31 in

General

Die Index	40
Trade Name	HYLUG™
Sub Brand	HYLUG
Physical Attribute - Tongue Type	Ring
Plated	Y
Feature - Barrel Type	Standard
Feature - Barrel Style	Chamfered
Construction Material - Main	Copper
Type	Ring Tongue
UPC 14 Digit GTIN	00781810085806
Material	Copper
Plating Type	Nickel
UPC	781810085806

Logistics

Minimum Pack Quantity	200
Carton Quantity	200

Pallet Quantity

79200

Product Assets

[Catalog \[English\]](#)



A Hubbell brand

© 2026 Hubbell Incorporated. All rights reserved
BRDY-YAV4CL2NK-SPEC-EN | REV 4/2026