



YAV4CL2TC14FXSL, Compression Terminal, 4 Flex G,H,I,K,M, DLO, 4 AWG, Cu, 2-Hole, 1/4" Stud, Slotted, Standard Barrel

By Burndy

Catalog # [YAV4CL2TC14FXSL](#)

Copper Compression Terminal

Features

- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding
- For applications greater than 2000 Volts consult cable manufacturer for voltage stress relief instructions

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Wire Size	4 AWG
Conductor - Copper Flex K Size	4 AWG
Range	
Conductor - Copper Flex K Size	"4 AWG"
Conductor - Copper Flex M Size	"4 AWG"
Conductor - Copper Str Size	"4 AWG"
Conductor - Copper Flex I Size	4 AWG
Range	
Conductor - Copper Flex G Size	"4 AWG"
Conductor - Copper DLO Size	4 AWG
Range	
Conductor - Copper Str	"4 AWG"
Compact Size	
Conductor - Copper DLO Size	4 AWG
Conductor Size	4 AWG
Conductor - Copper Flex H Size	"4 AWG"
Conductor - Copper Flex G Size	4 AWG
Range	
Conductor - Copper Str Navy	40 (19) Navy-50 (19) Navy
Size Range	
Conductor - Copper Str Navy	40
Size	



Conductor - CopperWeld Str Size

- 4 A AWG
- 4 D AWG
- 4 N AWG
- 4 P AWG

Conductor Type CODE/FLEX

Conductor - Copper Str Size Range 4 AWG

Conductor - Copper Flex H Size Range 4 AWG

Conductor - Copper Flex I Size "4 AWG"

Configuration

Physical Attribute - Number of Holes	2
Number of Pad Holes	2
Connector Type	STANDARD BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	0.55 in
Package Height	0.000 in
Dimension - Height mm	0 mm
Dimension - Hole Size fraction	1/4
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	53 mm
Dimension - Outside Diameter inch	0.38 in
Width	0.55 in
Dimension - Hole Size mm	6.9 mm
Dimension - Hole Size inch	0.27
Dimension - Strip Length inch	1/2 in
Dimension - Stud Size inch	1/4
Dimension - Stud Size fraction	1/4
Dimension - Bolt Hole Size inch	0.27 in
Dimension - Bolt Size fraction	1/4
Length	2.08 in
Physical Attribute - Tongue Angle	Straight
Dimension - Z inch	0.32 in
Dimension - B Length inch	0.50 in

Height	0.09 in	UPC	781810459263
Dimension - N inch	0.31 in	Type	Standard Barrel, Tin Plated
Dimension - Bolt Size inch	0.25	Material	Copper
Dimension - Length Overall inch	2.08 in	Plating Type	Tin - Electro Plated
Dimensions	2.08 in x 0.55 in x 0.09 in	Finish Type	Tin-Plated
		UPC 12 Digit	781810459263
		UPC 14 Digit GTIN	00781810459263
General		Logistics	
Trade Name	HYLUG™	Minimum Pack Quantity	50
Die Index	8	Carton Quantity	50
Feature - Barrel Type	Standard		
Feature - Barrel Style	Chamfered		
Plated	Yes		
Color Code	Gray	Product Assets	
		Catalog [English]	



A Hubbell brand