



YAV4CL5NK, Uninsulated Ring Terminal For 4 AWG, 1-Hole, 1/2" Stud, Nickel Plated

By Burndy
Catalog # [YAV4CL5NK](#)

Uninsulated Ring Terminal For 4 AWG (Nickel Plated)



Features

- Nickel plated for high temperature applications up to 650°F continuous service and 750°F intermittent service
- Manufactured from seamless pure electrolytic copper tubing to provide maximum conductivity, low resistance, and excellent ductility for crimping
- Double thick tongue provides a structurally strong terminal tongue
- Produced from tubular copper, extra copper material assures the ompression terminal will operate cooler than the conductors it connects
- Internally beveled barrel for easy cable entry, especially for flexible conductors
- Inspection hole provides easy visual check for proper conductor insertion

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor - Copper Solid Size	4
Conductor - Copper Str Aircraft Size	AN 4
Conductor Size	4 AWG
Conductor - Copper Str Size	4
Conductor - Copper Str Size Range	4 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Ring Terminal

Dimensions

Package Length	0.000 in
----------------	----------

Package Width	0.000 in
Dimension - B Length fraction	1/2 in
Package Weight	0.000 lb.
Dimension - B Length inch	0.47 in
Dimension - Outside Diameter inch	0.38 in
Dimension - Z inch	0.47 in
Dimension - Pad Width inch	0.73 in
Physical Attribute - Tongue Angle	Straight
Package Height	0.000 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - Hole Size mm	13 mm
Dimension - Inside Diameter inch	0.28 in
Dimension - Strip Length inch	1/2
Dimension - Stud Size inch	1/2 in
Dimension - Length Overall inch	1.68 in
Dimension - N inch	0.38 in

General

Die Index	40
Physical Attribute - Tongue Type	Ring
Trade Name	HYLUG™
Plated	Y
Feature - Barrel Type	Standard
Feature - Barrel Style	Chamfered
Type	Ring Tongue
UPC 14 Digit GTIN	00781810348666
Material	Copper
Plating Type	Nickel
UPC	781810348666

Logistics

Minimum Pack Quantity	200
Carton Quantity	200
Pallet Quantity	92800

Product Assets

[Catalog \[English\]](#)

