



YAV4CLNK, Uninsulated Ring Terminal For 4 AWG, 1-Hole, 1/4" Stud, Nickel Plated

By Burndy
Catalog # [YAV4CLNK](#)

Uninsulated Ring Terminal For 4 AWG (Nickel Plated)



Features

- Nickel plated for high temperature applications up to 650°F continuous service and 750°F intermittent service
- Manufactured from seamless pure electrolytic copper tubing to provide maximum conductivity, low resistance, and excellent ductility for crimping
- Double thick tongue provides a structurally strong terminal tongue
- Produced from tubular copper, extra copper material assures the ompression terminal will operate cooler than the conductors it connects
- Internally beveled barrel for easy cable entry, especially for flexible conductors
- Inspection hole provides easy visual check for proper conductor insertion

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	Yes
UL Listed	Yes

Conductor

Conductor - Copper Flex K Size	4
Conductor - Copper Flex M Size	4
Conductor - Copper Str Aircraft Size	AN 4
Conductor - Copper Flex G Size	4
Conductor - Copper Flex H Size	4
Conductor Size	4 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size
Conductor - Copper Flex I Size	4

Configuration

Physical Attribute - Number of Holes	1
--------------------------------------	---

Connector Type

Ring Terminal

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - Pad Width inch	0.55 in
Package Height	0.000 in
Dimension - Strip Length inch	1/2
Dimension - Stud Size inch	1/4 in
Dimension - B Length fraction	1/2 in
Dimension - B Length inch	0.47 in
Dimension - Z inch	0.28 in
Physical Attribute - Tongue Angle	Straight
Dimension - Bolt Hole Size inch	0.27 in
Dimension - Bolt Size fraction	1/4
Dimension - Length Overall inch	1.37 in
Dimension - N inch	0.25 in

General

Die Index	40
Trade Name	HYLUG™
Physical Attribute - Tongue Type	Ring
Plated	Y
Feature - Barrel Type	Standard
Feature - Barrel Style	Chamfered
Type	Ring Tongue
UPC 14 Digit GTIN	00781810096789
Material	Copper
Plating Type	Nickel
UPC	781810096789

Logistics

Minimum Pack Quantity	200
Carton Quantity	200
Pallet Quantity	79200

Product Assets

[Catalog \[English\]](#)

