



YAV6CL26CG1, Compression Terminal, AN-6, 1-Hole, 3/8" Stud, Standard Barrel

By Burndy

Catalog # [YAV6CL26CG1](#)

Copper Compression Terminal



Features

- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding
- For applications greater than 2000 Volts consult cable manufacturer for voltage stress relief instructions

Application

Wire Termination

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Flex G Size	"6 AWG"
Conductor - Copper Str	"6 AWG"
Compact Size	
Conductor - Copper DLO Size	6 AWG
Conductor Size	6 AWG
Conductor - Copper Flex H Size	"6 AWG"
Conductor - Copper Str Navy	30
Size	
Conductor - Copper Str Aircraft	AN 6
Size Range	
Conductor - Copper Str Aircraft	AN 6
Size	
Conductor - Material	COPPER
Wire Size	6 AWG
Conductor - Copper Flex K Size	"6 AWG"
Conductor - Copper Flex M Size	"6 AWG"
Conductor Type	CODE/FLEX
Conductor - Copper Str Size	"6 AWG"
Conductor - Copper Flex I Size	"6 AWG"

Configuration

Physical Attribute - Number of Holes	1
--------------------------------------	---

Number of Pad Holes	2
Connector Type	STANDARD BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	0.60 in
Dimension - Bolt Hole Size inch	0.44 in
Package Height	0.000 in
Dimension - Hole Size fraction	3/8
Dimension - Bolt Size fraction	3/8
Length	1.39 in
Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	1/2 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Z inch	0.36 in
Dimension - L Length Overall mm	35 mm
Dimension - B Length inch	0.50 in
Height	0.06 in
Width	0.6 in
Dimension - N inch	0.30 in
Dimension - Hole Size mm	10.4 mm
Dimension - Bolt Size inch	0.38
Dimension - Hole Size inch	0.41
Dimension - Length Overall inch	1.39 in
Dimension - Stud Size fraction	3/8
Dimensions	1.39 in x 0.6 in x 0.06 in

General

Feature - Barrel Type	Standard
Feature - Barrel Style	• Chamfered • Skived
Plated	Y
Trade Name	HYLUG™
Physical Attribute - Tongue Type	Ring
Die Index	7
UPC	621945123311
Type	Standard Barrel, Tin Plated

Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	621945123311
UPC 14 Digit GTIN	00621945123311

Logistics	
Minimum Pack Quantity	50
Carton Quantity	50

Product Assets

[Catalog \[English\]](#)



A Hubbell brand