



YAV6CL2NK, Compression Terminal, #6 Str, 1-Hole, 3/8" Stud, Standard Barrel, Nickel Plated

By Burndy

Catalog # [YAV6CL2NK](#)

Copper Compression Terminal



Features

- Seamless, heavy duty uninsulated compression terminal provides a strong connector for demanding applications requiring high reliability
- Suitable for use on Type AN aircraft cable, extra flexible conductors and commercial (code) conductors

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Material	COPPER
Wire Size	6 AWG
Conductor - Copper Flex K Size	"6 AWG"
Conductor - Copper Flex M Size	"6 AWG"
Conductor - Copper Str Size	"6 AWG"
Conductor - Copper Flex G Size	"6 AWG"
Conductor - Copper Str	"6 AWG"
Compact Size	
Conductor - Copper DLO Size	6 AWG
Conductor Size	6 AWG
Conductor - Copper Flex H Size	"6 AWG"
Conductor - Copper Str Navy Size	30
Conductor Type	CODE/FLEX
Conductor - Copper Str Size Range	6 AWG
Conductor - Copper Flex I Size	"6 AWG"

Configuration

Physical Attribute - Number of Holes	1
Number of Pad Holes	2
Connector Type	STANDARD BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	0.60 in
Package Height	0.000 in
Dimension - Hole Size fraction	3/8
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	36 mm
Dimension - Outside Diameter inch	0.31 in
Dimension - Hole Size mm	10.4 mm
Dimension - Hole Size inch	0.41
Dimension - Stud Size fraction	3/8
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Physical Attribute - Tongue Angle	Straight
Dimension - B Length inch	0.47 in
Dimension - D inch	0.65 in
Dimension - N inch	0.30 in
Dimension - Bolt Size inch	0.38
Dimension - Length Overall inch	1.43 in

General

Trade Name	HYLUG™
Die Index	7
Feature - Barrel Type	Standard
Feature - Barrel Style	- Chamfered - Skived
Plated	Y
Color Code	Blue
Physical Attribute - Tongue Type	Ring
UPC	781810069677
Type	Standard Barrel, Nickel Plated
Material	Copper
Plating Type	Nickel
Finish Type	Nickel Plated
UPC 12 Digit	781810069677

UPC 14 Digit GTIN	00781810069677	Carton Quantity	200
Logistics		Product Assets	
Minimum Pack Quantity	1	Catalog [English]	
Pallet Quantity	92800		

