



YAV6CLNK, Ring Terminal, 6 AWG, 1-Hole, 1/4" Stud (Nickel)

By Burndy
Catalog # [YAV6CLNK](#)

Seamless, Uninsulated Ring Terminal, 1-Hole, 1/4" Stud, Standard Barrel, Nickel Plated



Features

- Nickel plated for high temperature applications up to 650°F continuous service and 750°F intermittent service
- Manufactured from seamless pure electrolytic copper tubing to provide maximum conductivity, low resistance, and excellent ductility for crimping
- Double thick tongue provides a structurally strong terminal tongue
- Produced from tubular copper, extra copper material assures the ompression terminal will operate cooler than the conductors it connects
- Internally beveled barrel for easy cable entry, especially for flexible conductors
- Inspection hole provides easy visual check for proper conductor insertion

Application

For Use On Type AN Aircraft Cable, Extra Flexible Conductors And Commercial (Code) Conductors, Industrials, Hospitals, Electric Utilities, Marine, Computers, And Other Equipment Subject To Vibration Or Requiring Dependable Electrical Performance

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	6 AWG
Conductor Size	6 AWG
Conductor Type	- CU C Solid-Size - CU C Str-Size
Conductor - Copper Str Size Range	6 AWG

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Ring Terminal

Dimensions

Dimension - Pad Width inch	0.48 in
Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Outside Diameter inch	0.31 in
Dimension - Hole Size mm	7 mm
Dimension - Strip Length inch	1/2
Dimension - Stud Size inch	1/4 in
Dimension - Bolt Hole Size inch	0.27 in
Dimension - Bolt Size fraction	1/4
Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	1/2 in
Dimension - Z inch	0.29 in
Dimension - B Length inch	0.47 in
Dimension - N inch	0.25 in
Dimension - Length Overall inch	1.31 in

General

Product Family	COMPRESSION
Trade Name	HYLUG™
Die Index	39
Feature - Barrel Type	Standard
Feature - Barrel Style	Chamfered
Plated	Yes
Physical Attribute - Tongue Type	Ring
Sub Brand	TERMINALS, HYLUG
Product Type	Terminal
UPC	781810095263
Type	Ring Tongue
Material	Copper
Plating Type	Nickel
UPC 14 Digit GTIN	00781810095263

Logistics

Minimum Pack Quantity	200
Pallet Quantity	99999
Carton Quantity	200

Product Assets

[Catalog \[English\]](#)



A Hubbell brand