



YAV6CLTC38FX90, Compression Terminal, 6 Flex G,H,I,K,M, DLO, 6 AWG, Cu, 1-Hole, 3/8" Stud, Standard Barrel, 90 Degree

By Burndy

Catalog # [YAV6CLTC38FX90](#)

6 Flex G,H,I,K,M,DLO, 6 AWG, CU, 1 Hole, 3/8 Stud, Standard
Barrel, Inspection Window, 90 Degree

Features

- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding
- For applications greater than 2000 Volts consult cable manufacturer for voltage stress relief instructions

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Wire Size	6 AWG
Conductor - Copper Flex K Size Range	6 AWG
Conductor - Copper Flex K Size	"6 AWG"
Conductor - Copper Flex M Size Range	6 AWG
Conductor - Copper Flex M Size	"6 AWG"
Conductor - Copper Str Size	"6 AWG"
Conductor - Copper Flex I Size Range	6 AWG
Conductor - Copper Flex G Size	"6 AWG"
Conductor - Copper DLO Size Range	6 AWG
Conductor - Copper Str Compact Size	"6 AWG"
Conductor - Copper DLO Size	6 AWG
Conductor Size	6 AWG
Conductor - Copper Flex H Size	"6 AWG"
Conductor - Copper Flex G Size Range	6 AWG



Conductor - Copper Str Navy Size Range	30 Navy
Conductor - Copper Str Navy Size	30
Conductor - Copper Solid Size Range	6 AWG
Conductor - Copper Solid Size	6 Sol
Conductor Type	CODE/FLEX
Conductor - Copper Str Size Range	6 AWG
Conductor - Copper Flex H Size Range	6 AWG
Conductor - Copper Flex I Size	"6 AWG"

Configuration

Physical Attribute - Number of Holes	1
Number of Pad Holes	1
Connector Type	STANDARD BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	0.58 in
Package Height	0.000 in
Dimension - Height mm	22.1 mm
Dimension - Hole Size fraction	3/8
Dimension - Height inch	0.87 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	27 mm
Dimension - Outside Diameter inch	0.31 in
Dimension - Hole Size mm	10.4 mm
Dimension - Hole Size inch	0.41
Dimension - Strip Length inch	1/2 in
Dimension - Stud Size fraction	3/8
Dimension - Bolt Hole Size inch	0.40 in
Dimension - Bolt Size fraction	3/8
Physical Attribute - Tongue Angle	90 Degree

Angle - Pad	90 °	Physical Attribute - Tongue	Standard
Dimension - B Length fraction	1/2 in	Type	
Dimension - Z inch	0.42 in	UPC	781810080498
Dimension - B Length inch	0.50 in	Type	Standard Barrel, Tin Plated
Dimension - N inch	0.41 in	Material	Copper
Dimension - Bolt Size inch	0.38	Plating Type	Tin - Electro Plated
Dimension - Length Overall	1.06 in	Finish Type	Tin-Plated
inch		UPC 12 Digit	781810080498
		UPC 14 Digit GTIN	00781810080498
General		Logistics	
Trade Name	HYLUG™	Minimum Pack Quantity	50
Die Index	7	Carton Quantity	50
Feature - Barrel Type	Standard		
Feature - Barrel Style	• Chamfered • Skived		
Plated	Y	Product Assets	
Color Code	Blue	Catalog [English]	



A Hubbell brand