



YAV702M8, Compression Terminal

By Burndy

Catalog # [YAV702M8](#)



HYLUG™ Copper tubing Compression terminals, Metric, 2 Holes
With Inspection Window, 70mm² Class2, M8 stud, Tin - Electro
Plated.

Features

- Barrel is designed with an internal chamfer at the wire entry to ensure smooth insertion of the wire, preventing possible damaging of the strands
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive
- Compatible Standards: IEC61238-1, UL 486A-486B, CSA-C22.2 No. 65-03

Application

Metric Wire Termination

General

Catalog Number	YAV702M8
Connector Type	METRIC
Die Index	13
Feature - Barrel Style	• Chamfered • Skived
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810637913
UPC 14 Digit GTIN	00781810637913

Dimensions

Dimension - B Length inch	0.69 in
Dimension - Bolt Size fraction	5/16
Dimension - Bolt Size inch	0.3125
Dimension - Hole Size fraction	5/16
Dimension - Hole Size inch	0.38
Dimension - Hole Size mm	10 mm
Dimension - L Length Overall mm	91 mm

Dimension - Length Overall inch	3.57 in
Dimension - Pad Width inch	0.83 in
Dimension - Strip Length inch	0.748 in
Dimension - Stud Size fraction	5/16
Dimension - Stud Size inch	M8
Dimension - Z (inch)	0.36 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Str Size	70 mm² (1/0 AWG)
Conductor - Copper Str Size Range	70 mm² (1/0 AWG)
Conductor - Material	COPPER
Conductor Size	70 mm2
Conductor Type	CLASS 2

Certifications And Compliance

Standards - RoHS Compliance Status	CM
------------------------------------	----

Logistics

Minimum Pack Quantity	20
-----------------------	----

Product Assets

[3D Models - YAV702M8_MODEL-PDF](#)
[3D Models - YAV702M8_MODEL-IGES](#)
[3D Models - YAV702M8_MODEL-STEP](#)
[Catalogs - BURNDY Master Catalog - Section C - Compression Connections](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_yavm_lineart](#)
[Sales Drawings - 50025887](#)
[Specifications - YAV702M8](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved
BRDY-YAV702M8-SPEC-EN | REV 7/2025