



YAV9CT4BOX, Uninsulated Ring Terminal For 10 - 9 AWG

By Burndy

Catalog # [YAV9CT4BOX](#)

Uninsulated Ring Terminal For 10 - 9 AWG



Features

- Manufactured from seamless pure electrolytic copper tubing to provide maximum conductivity, low resistance and excellent ductility for crimping
- Seamless tubular crimp barrel design - No seams to split resulting in a very high quality electrical connection, also can be used on solid conductor
- Double thick tongue structurally a very strong terminal tongue
- Produced from tubular copper, extra copper material assures the compression connector will operate cooler than the conductors it connects
- Internally bevelled barrel for easy cable entry, especially for flexible conductors
- Inspection hole provides easy visual check for proper conductor insertion
- Electro-tin plated for a long lasting durable corrosion resistance

Specifications


Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
Industry Standard(s)	UL467
Certification - CSA Approved	Yes
UL Listed	Yes

Conductor

Conductor Size	10 - 9 AWG
Conductor - Copper Str Size	• 10 AWG • 9 AWG
Conductor - Copper Str Size Range	10 AWG - 9 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size

Configuration

Physical Attribute - Number of Holes	1
--------------------------------------	---



Connector Type

Ring Terminal

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length fraction	2/5 in
Package Weight	0.000 lb.
Dimension - B Length inch	0.39 in
Dimension - Outside Diameter inch	0.23 in
Dimension - Z inch	0.36 in
Dimension - L Length Overall mm	31 mm
Dimension - Pad Width inch	0.52 in
Package Height	0.000 in
Dimension - Hole Size fraction	32/97
Dimension - Bolt Size fraction	5/16
Dimension - Hole Size inch	0.33 in
Dimension - Strip Length inch	7/16 in
Dimension - Stud Size inch	5/16"
Dimension - Length Overall inch	1.23 in
Dimension - D inch	0.34 in
Dimension - N inch	0.27 in

General

Physical Attribute - Tongue Type	Ring
Trade Name	HYLUG™
Plated	Y
Feature - Barrel Style	Chamfered
Type	Ring Tongue
UPC 14 Digit GTIN	00781810532201
Material	Copper
Plating Type	Tin - Electro Plated
UPC	781810532201

Logistics

Minimum Pack Quantity	50
Carton Quantity	600
Pallet Quantity	99999

Product Assets

[Catalog \[English\]](#)