



**YAZ29TC1290, Compression Terminal, 250
kcmil Cu, 1-Hole, 1/2" Stud, Long Barrel, 90
Degree**

By Burndy

Catalog # [YAZ29TC1290](#)

250 kcmil, CU, 1 Hole, 1/2 Stud, Long Barrel, Inspection Window,
90 Degree



Features

- Barrel is designed with an internal chamfer at the wire entry to ensure smooth insertion of the wire, preventing possible damaging of the strands
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding

Application

Wire Termination

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor Size	250 KCMIL
Conductor - Copper Str Navy Size Range	250 (61) Navy
Conductor - Copper Str Navy Size	250 (61) Navy
Conductor - Material	COPPER
Conductor Type	CODE
Conductor - Copper Str Size	250 KCMIL

Configuration

Physical Attribute - Number of Holes	1
Number of Pad Holes	1
Connector Type	LONG BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions



A Hubbell brand

Dimension - Pad Width inch	1.10 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Hole Size fraction	1/2
Dimension - Bolt Size fraction	1/2
Physical Attribute - Tongue Angle	90 Degree
Dimension - Height inch	2.42 in
Angle - Pad	90 °
Dimension - Z inch	0.55 in
Dimension - L Length Overall mm	40 mm
Dimension - B Length inch	1.62 in
Dimension - Outside Diameter inch	0.75 in
Dimension - N inch	0.53 in
Dimension - Hole Size mm	13.5 mm
Dimension - Bolt Size inch	0.5
Dimension - Hole Size inch	0.53
Dimension - Length Overall inch	1.58 in
Dimension - Strip Length inch	1-11/16
Dimension - Stud Size fraction	1/2

General

Feature - Barrel Type	Long
Feature - Barrel Style	Skived
Plated	Yes
Color Code	Yellow
Trade Name	HYLUG™
Die Index	16
UPC	781810240205
Type	Long Barrel, Skive, Tin Plated
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810240205
UPC 14 Digit GTIN	00781810240205

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalog \[English\]](#)