



YAZ2C2NTC38, Compression Terminal, 2 AWG Cu, 2-Hole, 3/8" Stud, 1-3/4" Spacing, Long Barrel

By Burndy

Catalog # [YAZ2C2NTC38](#)

2 AWG, CU, 2 Hole, 3/8 Stud, 1-3/4 IN Spacing, Long Barrel,
Inspection Window



Features

- Barrel is designed with an internal chamfer at the wire entry to ensure smooth insertion of the wire, preventing possible damaging of the strands
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	TAA Compliant (All status valid till December 2026)
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Conductor - Copper Str Size	2 AWG
Conductor Size	2 AWG
Conductor - Copper Str Navy	60 (37) Navy
Size Range	
Conductor - Copper Str Navy	60 (37) Navy
Size	
Conductor Type	CODE

Configuration

Physical Attribute - Number of Holes	2
Number of Pad Holes	2
Connector Type	LONG BARREL

Current

Voltage Rating	35 kV
----------------	-------

Voltage - Maximum	35000
-------------------	-------

Dimensions

Dimension - Pad Width inch	0.60 in
Package Height	0.000 in
Dimension - Hole Size fraction	3/8
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	106 mm
Dimension - Outside Diameter inch	0.42 in
Dimension - Hole Size mm	10.4 mm
Dimension - Hole Size inch	0.41
Dimension - Strip Length inch	1-5/16
Dimension - Stud Size inch	3/8
Dimension - Stud Size fraction	3/8
Dimension - Bolt Hole Size inch	0.4 in
Dimension - Bolt Size fraction	3/8
Physical Attribute - Tongue Angle	Straight
Dimension - Z inch	2.18 in
Dimension - B Length inch	1.25 in
Dimension - N inch	0.41 in
Dimension - Bolt Size inch	0.38
Dimension - Length Overall inch	4.16 in

General

Trade Name	HYLUG™
Die Index	10
Feature - Barrel Type	Long
Feature - Barrel Style	Skived
Plated	Yes
Color Code	Brown
Sub Brand	HYLUG
UPC	781810227756
Type	Long Barrel, Skive, Tin Plated
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810227756
UPC 14 Digit GTIN	00781810227756

Logistics

Minimum Pack Quantity	1
Pallet Quantity	24000
Carton Quantity	25

Product Assets

- [Catalog \[English\]](#)
- [Installation Manual \[English\]](#)
- [Installation Manual \[French, English\]](#)

