



YAZ2C2TC1490, Compression Terminal, 2 AWG Cu, 2-Hole, 1/4" Stud, 5/8" Spacing, Long Barrel, 90 Degree

By Burndy

Catalog # [YAZ2C2TC1490](#)

2 AWG, CU, 2 Hole, 1/4 Stud, 5/8 IN Spacing, Long Barrel, Inspection Window, 90 Degree

Features

- Barrel is designed with an internal chamfer at the wire entry to ensure smooth insertion of the wire, preventing possible damaging of the strands
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Conductor - Copper Str Size	2 AWG
Conductor Size	2 AWG
Conductor - Copper Str Navy Size Range	60 (37) Navy
Conductor - Copper Str Navy Size	60 (37) Navy
Conductor Type	CODE

Configuration

Physical Attribute - Number of Holes	2
Number of Pad Holes	2
Connector Type	LONG BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000



Dimensions

Dimension - Pad Width inch	0.60 in
Package Height	0.000 in
Dimension - Hole Size fraction	1/4
Dimension - Height inch	1.74 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	40 mm
Dimension - Outside Diameter inch	0.42 in
Dimension - Hole Size mm	6.9 mm
Dimension - Hole Size inch	0.27
Dimension - Strip Length inch	1-5/16
Dimension - Stud Size fraction	1/4
Dimension - Bolt Hole Size inch	0.27 in
Dimension - Bolt Size fraction	1/4
Physical Attribute - Tongue Angle	90 Degree
Angle - Pad	90 °
Dimension - Z inch	0.96 in
Dimension - B Length inch	1.25 in
Dimension - N inch	0.31 in
Dimension - Bolt Size inch	0.25
Dimension - Length Overall inch	1.58 in

General

Trade Name	HYLUG™
Die Index	10
Feature - Barrel Type	Long
Feature - Barrel Style	Skived
Plated	Yes
Color Code	Brown
Physical Attribute - Tongue Type	Standard
Sub Brand	TERMINALS, HYLUG
UPC	781810229262
Type	Long Barrel, Skive, Tin Plated
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810229262
UPC 14 Digit GTIN	00781810229262

Logistics

Minimum Pack Quantity	1
Pallet Quantity	23200

Carton Quantity50

Product Assets

[Catalog \[English\]](#)



A Hubbell brand