



YAZ312NTCFX, Compression Terminal, 250 kcmil I,K,M, 262 DLO, Cu, 2-Hole, 1/2" Stud, 1-3/4" Spacing, Long Barrel

By Burndy

Catalog # [YAZ312NTCFX](#)

250 kcmil I, K, M, 262 DLO, CU, 2 Hole, 1/2 Stud, 1-3/4 IN Spacing, Long Barrel, Inspection Window

Features

- Barrel is designed with an internal chamfer at the wire entry to ensure smooth insertion of the wire, preventing possible damaging of the strands
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Wire Size	250 KCMIL
Conductor - Copper Flex K Size Range	4/0 AWG
Conductor - Copper Flex K Size	250 kcmil
Conductor - Copper Flex M Size	250 KCMIL
Conductor - Copper Str Size	250 KCMIL
Conductor - Copper Flex I Size Range	4/0 AWG
Conductor - Copper DLO Size Range	4/0 AWG
Conductor - Copper DLO Size	262 KCMIL
Conductor Size	250 KCMIL
Conductor - Copper Flex G Size Range	4/0 AWG
Conductor Type	FLEX
Conductor - Copper Str Size Range	250 kcmil



Conductor - Copper Flex H Size Range	4/0 AWG
Conductor - Copper Flex I Size	250 KCMIL

Configuration

Physical Attribute - Number of Holes	2
Number of Pad Holes	2
Connector Type	LONG BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	1.29 in
Package Height	0.000 in
Dimension - Hole Size fraction	1/2
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	143 mm
Dimension - Outside Diameter inch	0.88 in
Dimension - Thread Size	1/2
Dimension - Hole Size mm	14 mm
Dimension - Hole Size inch	0.56
Dimension - Strip Length inch	2-1/16
Dimension - Stud Size fraction	1/2
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	2 in
Dimension - Z inch	0.65 in
Dimension - B Length inch	2.00 in
Dimension - Length Side B inch	5.64 in
Dimension - D inch	3.02 in
Dimension - N inch	0.62 in
Dimension - Bolt Size inch	0.5
Dimension - Length Overall inch	5.64 in

General

Trade Name	HYLUG™
Die Index	17
Feature - Barrel Type	Long
Feature - Barrel Style	Skived
Plated	Y
Color Code	White
Sub Brand	HYLUG
UPC	781810228609
Type	Long Barrel, Skive
Material	Copper
Plating Type	Tin
Finish Type	Tin-Plated
UPC 12 Digit	781810228609
UPC 14 Digit GTIN	00781810228609

Logistics

Minimum Pack Quantity	25
Pallet Quantity	7400
Carton Quantity	25

Operational

Temperature Rating	194
--------------------	-----

Product Assets

- [Catalog \[English\]](#)
- [Installation Manual \[English\]](#)
- [Installation Manual \[French, English\]](#)



A Hubbell brand