



YAZ312TC14E2, Compression Terminal, 350 kcmil Cu, 2-Hole, 1/4" Stud, 3/4" Spacing, Long Barrel

By Burndy
Catalog # [YAZ312TC14E2](#)

350 kcmil, CU, 2 Hole, 1/4 Stud, 3/4 IN Spacing, Long Barrel, Inspection Window

Features

- Barrel is designed with an internal chamfer at the wire entry to ensure smooth insertion of the wire, preventing possible damaging of the strands
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Buy America(n) Qualified	TAA Compliant (All status valid till December 2026)
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Conductor - Copper Str Size	350 KCMIL
Conductor Size	350 KCMIL
Conductor - Copper Str Navy Size	350 (91) Navy
Conductor Type	CODE

Configuration

Physical Attribute - Number of Holes	2
Number of Pad Holes	2
Connector Type	LONG BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions



Dimension - Pad Width inch	1.29 in
Package Height	0.000 in
Dimension - Hole Size fraction	1/4
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	102 mm
Dimension - Outside Diameter inch	0.88 in
Dimension - Thread Size	1/4 in
Dimension - Hole Size mm	6.9 mm
Dimension - Hole Size inch	0.27
Dimension - Strip Length inch	2-1/16
Dimension - Stud Size inch	1/4
Dimension - Stud Size fraction	1/4
Dimension - Bolt Hole Size inch	0.27 in
Dimension - Bolt Size fraction	1/4
Physical Attribute - Tongue Angle	Straight
Dimension - Z inch	0.34 in
Dimension - B Length inch	2.00 in
Dimension - N inch	0.31 in
Dimension - Bolt Size inch	0.25
Dimension - Length Overall inch	4.02 in

General

Trade Name	HYLUG™
Die Index	18
Feature - Barrel Type	Long
Feature - Barrel Style	Skived
Plated	YES
Color Code	Red
Physical Attribute - Tongue Type	Standard
UPC	781810227909
Type	Long Barrel, Skive, Tin Plated
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810227909
UPC 14 Digit GTIN	00781810227909

Logistics

Minimum Pack Quantity	10
Carton Quantity	10

Product Assets

- Catalog [English]
- Installation Manual [English]
- Installation Manual [French, English]



A Hubbell brand