



YAZ32TC38FX, Compression Terminal, 300 kcmil G,H,I,K,M, 313 DLO, Cu, 1-Hole, 3/8" Stud, Long Barrel

By Burndy
Catalog # [YAZ32TC38FX](#)

300 kcmil G,H,I,K,M,313 DLO, CU, 1 Hole, 3/8 Stud, Long Barrel, Inspection Window

Features

- Barrel is designed with an internal chamfer at the wire entry to ensure smooth insertion of the wire, preventing possible damaging of the strands
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Wire Size	300 KCMIL
Conductor - Copper Flex K Size Range	300 kcmil
Conductor - Copper Flex K Size	300 KCMIL
Conductor - Copper Flex M Size Range	300 kcmil
Conductor - Copper Flex M Size	300 KCMIL
Conductor - Copper Str Size	300 KCMIL
Conductor - Copper Flex I Size Range	300 kcmil
Conductor - Copper Flex G Size	300 KCMIL
Conductor - Copper DLO Size Range	313 kcmil
Conductor - Copper DLO Size	313 KCMIL
Conductor Size	300 KCMIL
Conductor - Copper Flex H Size	300 KCMIL
Conductor - Copper Flex G Size Range	300 kcmil
Conductor Type	FLEX



Conductor - Copper Str Size Range	300 kcmil
Conductor - Copper Flex H Size Range	300 kcmil
Conductor - Copper Flex I Size	300 KCMIL

Configuration

Physical Attribute - Number of Holes	1
Number of Pad Holes	2
Connector Type	LONG BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	1.40 in
Package Height	0.000 in
Dimension - Hole Size fraction	3/8
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	92 mm
Dimension - Outside Diameter inch	0.95 in
Dimension - Hole Size mm	10.4 mm
Dimension - Hole Size inch	0.41
Dimension - Strip Length inch	2-3/16
Dimension - Stud Size inch	3/8
Dimension - Stud Size fraction	3/8
Dimension - Bolt Hole Size inch	0.40 in
Dimension - Bolt Size fraction	3/8
Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	2-1/8 in
Dimension - Z inch	0.42 in
Dimension - B Length inch	2.12 in
Dimension - N inch	0.41 in
Dimension - Bolt Size inch	0.38
Dimension - Length Overall inch	3.61 in

General

Trade Name	HYLUG™	UPC 12 Digit	781810241820
Die Index	18	UPC 14 Digit GTIN	00781810241820
Feature - Barrel Type	Long	Logistics	
Feature - Barrel Style	• Chamfered • Skived		
Plated	Y	Minimum Pack Quantity	10
Color Code	Red	Carton Quantity	10
UPC	781810241820	Product Assets	
Type	Long Barrel, Skive		
Material	Copper		
Plating Type	Tin	Catalog [English]	
Finish Type	Tin-Plated	Installation Manual [English]	
		Installation Manual [French, English]	



A Hubbell brand