



YAZ342NT38FX, Compression Terminal, 350 kcmil G, H, I, K, M, 373 DLO, Cu, 2-Hole, 3/8" Stud, 1" Spacing, Long Barrel, Narrow Tongue

By Burndy

Catalog # [YAZ342NT38FX](#)

350 kcmil G,H,I,K,M,373 DLO, CU, 2 Hole, 3/8 Stud, 1 IN Spacing, Long Barrel, Inspection Window

Features

- Barrel is designed with an internal chamfer at the wire entry to ensure smooth insertion of the wire, preventing possible damaging of the strands
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Yes
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Wire Size	350 KCMIL
Conductor - Copper Flex K Size Range	350 kcmil
Conductor - Copper Flex K Size	350 KCMIL
Conductor - Copper Flex M Size	350 KCMIL
Conductor - Copper Str Size	350 KCMIL
Conductor - Copper Flex I Size Range	350 kcmil
Conductor - Copper Flex G Size	350 KCMIL
Conductor - Copper DLO Size Range	373 kcmil
Conductor - Copper DLO Size	373 KCMIL
Conductor Size	350 kcmil
Conductor - Copper Flex H Size	350 KCMIL
Conductor - Copper Flex G Size Range	350 kcmil
Conductor Type	FLEX



Conductor - Copper Str Size Range	350 kcmil
Conductor - Copper Flex H Size Range	350 kcmil
Conductor - Copper Flex I Size	350 KCMIL

Configuration

Physical Attribute - Number of Holes	2
Number of Pad Holes	2
Connector Type	LONG BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	0.96 in
Package Height	0.000 in
Dimension - Hole Size fraction	3/8
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	123 mm
Dimension - Outside Diameter inch	1.06 in
Dimension - Hole Size mm	10.4 mm
Dimension - Hole Size inch	0.41
Dimension - Strip Length inch	2-5/16
Dimension - Stud Size inch	3/8 in
Dimension - Stud Size fraction	3/8
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	2-1/4 in
Dimension - Z inch	0.43 in
Dimension - B Length inch	2.25 in
Dimension - Length Side B inch	4.85 in
Dimension - Diameter Min Size inch	1.84 in
Dimension - N inch	0.41 in
Dimension - Bolt Size inch	0.38

Dimension - Length Overall inch	4.85 in	Material	Copper
		Plating Type	Tin - Electro Plated
		Finish Type	Tin-Plated
		UPC 14 Digit GTIN	00781810166055
General		Logistics	
Trade Name	HYLUG™	Minimum Pack Quantity	1
Die Index	19	Pallet Quantity	3600
Feature - Barrel Type	Long	Carton Quantity	50
Feature - Barrel Style	Skived		
Plated	Y		
Color Code	Blue		
Sub Brand	HYLUG		
UPC	781810166055		
Type	YAZ-2-NTFX, Long Barrel Narrow Tongue		
		Product Assets	
		Catalog [English]	
		Installation Manual [English]	
		Installation Manual [French, English]	



A Hubbell brand