



YAZ342TC38FXB, Compression Terminal, 373.3 kcmil 925/24, 2-Hole, 3/8" Stud, Long Barrel

By Burndy

Catalog # [YAZ342TC38FXB](#)

Copper Compression Terminal

Features

- Barrel is designed with an internal chamfer at the wire entry to ensure smooth insertion of the wire, preventing possible damaging of the strands
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Wire Size	350 KCMIL
Conductor - Copper Flex K Size	350 kcmil
Range	
Conductor - Copper Flex K Size	350 KCMIL
Conductor - Copper Flex M Size	350 KCMIL
Conductor - Copper Str Size	350 KCMIL
Conductor - Copper Flex I Size	350 kcmil
Range	
Conductor - Copper Flex G Size	350 KCMIL
Conductor - Copper DLO Size	373 kcmil
Range	
Conductor - Copper DLO Size	373 KCMIL
Conductor Size	350 kcmil
Conductor - Copper Flex H Size	350 KCMIL
Conductor - Copper Flex G Size	350 kcmil
Range	
Conductor Type	FLEX
Conductor - Copper Str Size	350 kcmil
Range	
Conductor - Copper Flex H Size	350 kcmil
Range	



Conductor - Copper Flex I Size 350 KCMIL

Configuration

Physical Attribute - Number of Holes	2
Number of Pad Holes	2
Connector Type	LONG BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	1.55 in
Package Height	0.000 in
Dimension - Hole Size fraction	3/8
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	129 mm
mm	
Dimension - Outside Diameter	1.06 in
inch	
Dimension - Hole Size mm	10.4 mm
Dimension - Hole Size inch	0.41
Dimension - Stud Size fraction	3/8
Dimension - Bolt Size fraction	3/8
Physical Attribute - Tongue	Straight
Angle	
Dimension - B Length fraction	2-1/2 in
Dimension - Z inch	0.43 in
Dimension - B Length inch	2.48 in
Dimension - N inch	0.41 in
Dimension - Inside Diameter	0.83 in
inch	
Dimension - Bolt Size inch	0.38
Dimension - Length Overall	5.09 in
inch	

General

Trade Name	HYLUG™
Die Index	19
Feature - Barrel Type	Long
Feature - Barrel Style	• Belled • Skived

Plated	Y	UPC 14 Digit GTIN	00781810277164
Color Code	Blue		
UPC	781810277164	Logistics	
Type	Long Barrel, Skive	Minimum Pack Quantity	6
Material	Copper	Carton Quantity	6
Plating Type	Tin - Electro Plated		
Finish Type	Tin-Plated	Product Assets	
UPC 12 Digit	781810277164	Catalog [English]	



A Hubbell brand