



YAZ362NT38G1, Compression Terminal, 600 kcmil Cu, 2-Hole, 3/8" Stud, Long Barrel

By Burndy

Catalog # [YAZ362NT38G1](#)

Copper Compression Terminal



Features

- Barrel is designed with an internal chamfer at the wire entry to ensure smooth insertion of the wire, preventing possible damaging of the strands
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding

Application

Wire Termination

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor Size	600 KCMIL
Conductor - Copper Solid Size	600
Conductor - Copper Solid Size Range	600
Conductor - Material	COPPER
Conductor Type	CODE
Conductor - Copper Str Size Range	600 kcmil
Conductor - Copper Str Size	600 KCMIL

Configuration

Physical Attribute - Number of Holes	2
Number of Pad Holes	1
Connector Type	LONG BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Bolt Hole Size inch	0.39 in
Package Height	0.000 in
Dimension - Hole Size fraction	3/8
Dimension - Bolt Size fraction	3/8
Length	6.27 in
Physical Attribute - Tongue Angle	Straight
Thickness	.26 in
Dimension - B Length fraction	2-11/16 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Z inch	0.53 in
Dimension - L Length Overall	168 mm
Dimension - B Length inch	2.69 in
Dimension - Outside Diameter inch	1.19 in
Dimension - N inch	0.75 in
Dimension - Hole Size mm	10.4 mm
Dimension - Bolt Size inch	0.38
Dimension - Hole Size inch	0.41
Dimension - Length Overall inch	6.61 in
Dimension - Strip Length inch	2-3/4
Dimension - Stud Size fraction	3/8

General

Feature - Barrel Type	Long
Feature - Barrel Style	• Chamfered • Skived
Plated	Y
Color Code	Green
Trade Name	HYLUG™
Die Index	22
UPC	781810283103
Type	Long Barrel, Skive, Tin Plated
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810283103
UPC 14 Digit GTIN	00781810283103

Logistics

Minimum Pack Quantity	25
Pallet Quantity	2775



A Hubbell brand