



YAZ362TC38FX, Compression Terminal, 500 kcmil G,H, 444 DLO, Cu, 2-Hole, 3/8" Stud, 1" Spacing, Long Barrel

By Burndy

Catalog # [YAZ362TC38FX](#)

500 kcmil G, H, 444 DLO, CU, 2 Hole, 3/8 Stud, 1 IN Spacing, Long Barrel, Inspection Window

Features

- Barrel is designed with an internal chamfer at the wire entry to ensure smooth insertion of the wire, preventing possible damaging of the strands
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Wire Size	500 KCMIL
Conductor - Copper Flex K Size Range	450 kcmil
Conductor - Copper Flex K Size	450 kcmil
Conductor - Copper Flex M Size Range	450 kcmil
Conductor - Copper Flex M Size	450 kcmil
Conductor - Copper Str Size	500 KCMIL
Conductor - Copper Flex I Size Range	500 kcmil
Conductor - Copper Flex G Size	500 KCMIL
Conductor - Copper DLO Size Range	444 kcmil
Conductor - Copper DLO Size	444 KCMIL
Conductor Size	500 KCMIL
Conductor - Copper Flex H Size	500 KCMIL
Conductor - Copper Flex G Size Range	450 kcmil
Conductor Type	FLEX



Conductor - Copper Str Size Range	500 kcmil
Conductor - Copper Flex H Size Range	500 kcmil
Conductor - Copper Flex I Size	450 kcmil

Configuration

Physical Attribute - Number of Holes	2
Number of Pad Holes	2
Connector Type	LONG BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	1.74 in
Package Height	0.000 in
Dimension - Hole Size fraction	3/8
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	141 mm
Dimension - Outside Diameter inch	1.19 in
Dimension - Hole Size mm	10.4 mm
Dimension - Hole Size inch	0.41
Dimension - Strip Length inch	2-3/4
Dimension - Stud Size fraction	3/8
Dimension - Bolt Hole Size inch	0.40 in
Dimension - Bolt Size fraction	3/8
Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	2-11/16 in
Dimension - Z inch	0.53 in
Dimension - B Length inch	2.69 in
Dimension - Length Side B inch	5.55 in
Dimension - N inch	0.50 in
Dimension - Bolt Size inch	0.38
Dimension - Length Overall inch	5.55 in

General

Trade Name	HYLUG™	UPC 14 Digit GTIN	00781810228647
Die Index	20	Logistics	
Feature - Barrel Type	Long		
Feature - Barrel Style	Skived		
Plated	Y		
Color Code	Brown		
UPC	781810228647	Minimum Pack Quantity	1
Type	Long Barrel, Skive	Pallet Quantity	2320
Material	Copper	Carton Quantity	10
Plating Type	Tin	Product Assets	
Finish Type	Tin-Plated		
UPC 12 Digit	781810228647		
		Catalog [English]	
		Installation Manual [English]	
		Installation Manual [French, English]	



A Hubbell brand