



YAZ38NT58FX, Compression Terminal, 535.3 (1324/24) DLO, 5/8" Stud, Long Barrel, Narrow Tongue

By Burndy

Catalog # [YAZ38NT58FX](#)

Copper Compression Terminal

Features

- Barrel is designed with an internal chamfer at the wire entry to ensure smooth insertion of the wire, preventing possible damaging of the strands
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding

Application

Wire Termination

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Copper Flex G Size	550 KCMIL
Conductor - Copper DLO Size	535 kcmil
Range	
Conductor - Copper DLO Size	535 KCMIL
Conductor Size	500-550 KCMIL
Conductor - Copper Flex H Size	500-550 KCMIL
Conductor - Copper Flex G Size	550 kcmil
Range	
Conductor - Material	COPPER
Wire Size	500-550 KCMIL
Conductor - Copper Flex K Size	500 kcmil
Range	
Conductor - Copper Flex K Size	500 KCMIL
Conductor - Copper Flex M Size	500 kcmil
Conductor Type	FLEX
Conductor - Copper Str Size	500 / 550 kcmil
Range	
Conductor - Copper Str Size	500-550 KCMIL
Conductor - Copper Flex H Size	500 / 550 kcmil
Range	
Conductor - Copper Flex I Size	500-550 KCMIL



Conductor - Copper Flex I Size 500 / 550 kcmil
Range

Configuration

Physical Attribute - Number of Holes	1
Number of Pad Holes	1
Connector Type	LONG BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	1.84 in
Dimension - Bolt Hole Size inch	0.66 in
Package Height	0.000 in
Dimension - Hole Size fraction	5/8
Dimension - Bolt Size fraction	5/8
Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	2-13/16 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Z inch	0.67 in
Dimension - L Length Overall mm	128 mm
Dimension - B Length inch	2.81 in
Dimension - Outside Diameter inch	1.25 in
Dimension - N inch	0.66 in
Dimension - Hole Size mm	17.5 mm
Dimension - Bolt Size inch	0.63
Dimension - Hole Size inch	0.69
Dimension - Length Overall inch	5.02 in
Dimension - Strip Length inch	2-7/8
Dimension - Stud Size inch	5/8 in
Dimension - Stud Size fraction	5/8

General

Feature - Barrel Type	Long
Feature - Barrel Style	Belled
Plated	Y

Color Code	Pink
Trade Name	HYLUG™
Die Index	L99
UPC	781810459140
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 14 Digit GTIN	00781810459140

Logistics

Minimum Pack Quantity	6
Pallet Quantity	2784
Carton Quantity	6

Product Assets

[Catalog \[English\]](#)



A Hubbell brand