



YAZ392NT38, Compression Terminal, 750 kcmil Cu, 2-Hole, 3/8" Stud, 1" Spacing, Long Barrel, Narrow Tongue

By Burndy
Catalog # YAZ392NT38

750 kcmil, CU, 2 Hole, 3/8 Stud, 1 IN Spacing, Long Barrel, Inspection Window

Features

- Barrel is designed with an internal chamfer at the wire entry to ensure smooth insertion of the wire, preventing possible damaging of the strands
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	TAA Compliant (All status valid till December 2026)
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Conductor - Copper Str Size	750 KCMIL
Conductor Size	750 KCMIL
Conductor Type	CODE
Conductor - Copper Str Size Range	750 kcmil

Configuration

Physical Attribute - Number of Holes	2
Number of Pad Holes	2
Connector Type	LONG BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	1.63 in
Package Height	0.000 in
Dimension - Hole Size fraction	3/8
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	148 mm
Dimension - Outside Diameter inch	1.30 in
Dimension - Hole Size mm	10.4 mm
Dimension - Hole Size inch	0.41
Dimension - Strip Length inch	2-15/16
Dimension - Stud Size inch	3/8
Dimension - Stud Size fraction	3/8
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	2-7/8 in
Dimension - Z inch	0.53 in
Dimension - B Length inch	2.88 in
Dimension - N inch	0.50 in
Dimension - Bolt Size inch	0.38
Dimension - Length Overall inch	5.82 in

General

Trade Name	HYLUG™
Die Index	24
Feature - Barrel Type	Long
Feature - Barrel Style	Skived
Plated	Y
Color Code	Black
Physical Attribute - Tongue Type	Standard
Sub Brand	HYLUG
UPC	781810211427
Type	YAZ-2N, Code Conductor Long Barrel
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 14 Digit GTIN	00781810211427



Logistics

Minimum Pack Quantity	1
Pallet Quantity	2784
Carton Quantity	6

Product Assets

- [Catalog \[English\]](#)
- [Installation Manual \[English\]](#)
- [Installation Manual \[French, English\]](#)



A Hubbell brand