



YAZ39NT12, Compression Terminal, 750 kcmil Cu, 1-Hole, 1/2" Stud, Long Barrel, Narrow Tongue

By Burndy

Catalog # [YAZ39NT12](#)



750 kcmil CU, One Hole, 1/2 Stud Size, Long Barrel, Inspection Window, Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, Black Color Code, 24 Die Index.

Features

- Barrel is designed with an internal chamfer at the wire entry to ensure smooth insertion of the wire, preventing possible damaging of the strands
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding

Application

Wire Termination

General

Catalog Number	YAZ39NT12
Color Code	Black
Connector Type	LONG BARREL
Die Index	24
Feature - Barrel Style	Skived
Feature - Barrel Type	Long
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
UPC	781810240700
UPC 14 Digit GTIN	00781810240700

Dimensions

Dimension - B Length fraction	2-7/8 in
Dimension - B Length inch	2.88 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - Bolt Size inch	0.5
Dimension - Hole Size fraction	1/2
Dimension - Hole Size inch	0.56
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	124 mm

Dimension - Length Overall inch	4.87 in
Dimension - N inch	0.53 in
Dimension - Outside Diameter inch	1.30 in
Dimension - Pad Width inch	1.63 in
Dimension - Strip Length inch	2-15/16
Dimension - Stud Size fraction	1/2
Dimension - Stud Size inch	1/2
Dimension - Z (inch)	0.55 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Str Size	750 KCMIL
Conductor - Copper Str Size Range	750 kcmil
Conductor - Material	COPPER
Conductor Size	750 KCMIL
Conductor Type	CODE

Certifications And Compliance

Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	10
Minimum Pack Quantity	10
Pallet Quantity	1440

Product Assets

[Catalogs - BURNDY Master Catalog - Section C - Compression Connections](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Installation Manuals - Copper Code Long Terminals Tooling and Installation Instructions](#)
[Installation Manuals - Medium & Large HYDENT Copper & Aluminum Terminal Crimp Instructions with 750 Series 12-Ton](#)

[Tool](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - SE..212356-31](#)
[Specifications - YAZ39NT12](#)
[Video - HYDENT Compression Terminal Overview Video](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved
BRDY-YAZ39NT12-SPEC-EN | REV 7/2025