



YAZ3C2TC14E290, Compression Terminal, 3 AWG Cu, 2-Hole, 1/4" Stud, 3/4" Spacing, Long Barrel, 90 Degree

By Burndy

Catalog # [YAZ3C2TC14E290](#)

3 AWG, CU, 2 Hole, 1/4 Stud, 3/4 IN Spacing, Long Barrel,
Inspection Window, 90 Degree

Features

- Barrel is designed with an internal chamfer at the wire entry to ensure smooth insertion of the wire, preventing possible damaging of the strands
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding

Application

Wire Termination

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor Size	3 AWG
Conductor - Copper Str Navy Size	50 (19) Navy
Conductor - Copper Solid Size	2 AWG
Conductor - Copper Solid Size Range	2 Sol
Conductor - Material	COPPER
Conductor Type	CODE
Conductor - Copper Str Size Range	3 AWG
Conductor - Copper Str Size	3 AWG

Configuration

Physical Attribute - Number of Holes	2
Number of Pad Holes	2
Connector Type	LONG BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000



Dimensions

Dimension - Pad Width inch	0.55 in
Dimension - Bolt Hole Size inch	0.27 in
Dimension - Hole Size fraction	1/4
Dimension - Bolt Size fraction	1/4
Physical Attribute - Tongue Angle	90 Degree
Dimension - Height inch	1.69 in
Angle - Pad	90 °
Dimension - B Length fraction	1-1/4 in
Dimension - Z inch	0.34 in
Dimension - L Length Overall mm	43 mm
Dimension - B Length inch	1.25 in
Dimension - Outside Diameter inch	0.38 in
Dimension - N inch	0.31 in
Dimension - Hole Size mm	6.9 mm
Dimension - Bolt Size inch	0.25
Dimension - Hole Size inch	0.27
Dimension - Length Overall inch	1.68 in
Dimension - Strip Length inch	1-5/16
Dimension - Stud Size fraction	1/4

General

Feature - Barrel Type	Long
Feature - Barrel Style	Skived
Plated	Y
Color Code	White
Trade Name	HYLUG™
Physical Attribute - Tongue Type	Standard
Die Index	9
UPC	781810229163
Type	Long Barrel, Skive, Tin Plated
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810229163
UPC 14 Digit GTIN	00781810229163

Logistics

Minimum Pack Quantity	1
-----------------------	---



A Hubbell brand