



YAZ442NNTFX, Cu Compression, 2-Hole, 1/2" Stud, 1-3/4" Spacing, Long Barrel, Narrow Tongue, 777.7 kcmil

By Burndy

Catalog # [YAZ442NNTFX](#)

HYLUG™ Copper Compression Terminal; Narrow Tongue; 2-Hole; Long Barrel

Features

- Barrel is designed with an internal chamfer at the wire entry to ensure smooth insertion of the wire, preventing possible damaging of the strands
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Wire Size	750 KCMIL
Conductor - Copper Flex K Size	750
Conductor - Copper Flex M Size	750
Conductor - Copper Str Size	750 KCMIL
Conductor - Copper Flex I Size Range	750 kcmil
Conductor - Copper Flex G Size	750 KCMIL
Conductor - Copper DLO Size Range	777 kcmil
Conductor - Copper DLO Size	777 KCMIL
Conductor Size	750 KCMIL
Conductor - Copper Flex H Size	750 KCMIL
Conductor - Copper Flex G Size Range	750 kcmil
Conductor Type	FLEX
Conductor - Copper Str Size Range	750 kcmil



Conductor - Copper Flex H Size Range 750 kcmil

Conductor - Copper Flex I Size 750 KCMIL

Configuration

Physical Attribute - Number of Holes	2
Number of Pad Holes	2
Connector Type	LONG BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	1.62 in
Package Height	0.000 in
Dimension - Hole Size fraction	1/2
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	180 mm
Dimension - Outside Diameter inch	1.50 in
Dimension - Hole Size mm	14 mm
Dimension - Hole Size inch	0.56
Dimension - Strip Length inch	3-1/16
Dimension - Stud Size inch	1/2 in
Dimension - Stud Size fraction	1/2
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	3 in
Dimension - Z inch	0.65 in
Dimension - B Length inch	3.00 in
Dimension - N inch	0.62 in
Dimension - Bolt Size inch	0.5
Dimension - Length Overall inch	7.09 in

General

Trade Name	HYLUG™
------------	--------

Die Index	L115	Finish Type	Tin-Plated
Feature - Barrel Type	Long	UPC 14 Digit GTIN	00781810166147
Feature - Barrel Style	Skived		
Plated	Y	Logistics	
Color Code	Yellow	Minimum Pack Quantity	1
Sub Brand	HYLUG	Pallet Quantity	1440
UPC	781810166147	Carton Quantity	20
Type	Narrow Tongue		
Material	Copper	Product Assets	
Plating Type	Tin	Catalog [English]	



A Hubbell brand