



YAZ442NT38FX, Cu Compression, 2-Hole, 3/8" Stud, 1" Spacing, Long Barrel, Narrow Tongue, 750 kcmil G, H, 777 DLO

By Burndy

Catalog # [YAZ442NT38FX](#)

750 kcmil G,H,777 DLO, CU, 2 Hole, 3/8 Stud, 1 IN Spacing, Long Barrel, Inspection Window

Features

- Barrel is designed with an internal chamfer at the wire entry to ensure smooth insertion of the wire, preventing possible damaging of the strands
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Wire Size	750 KCMIL
Conductor - Copper Flex K Size	750
Conductor - Copper Flex M Size	750
Conductor - Copper Str Size	750 KCMIL
Conductor - Copper Flex I Size Range	750 kcmil
Conductor - Copper Flex G Size	750 KCMIL
Conductor - Copper DLO Size Range	777 kcmil
Conductor - Copper DLO Size	777 KCMIL
Conductor Size	750 KCMIL
Conductor - Copper Flex H Size	750 KCMIL
Conductor - Copper Flex G Size Range	750 kcmil
Conductor Type	FLEX
Conductor - Copper Str Size Range	750 kcmil



Conductor - Copper Flex H Size Range	750 kcmil
Conductor - Copper Flex I Size	750 KCMIL

Configuration

Physical Attribute - Number of Holes	2
Number of Pad Holes	2
Connector Type	LONG BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	1.62 in
Package Height	0.000 in
Dimension - Hole Size fraction	3/8
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	155 mm
Dimension - Outside Diameter inch	1.50 in
Dimension - Hole Size mm	10.4 mm
Dimension - Hole Size inch	0.41
Dimension - Strip Length inch	3-1/16
Dimension - Stud Size inch	3/8 in
Dimension - Stud Size fraction	3/8
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	3 in
Dimension - Z inch	0.53 in
Dimension - B Length inch	3.00 in
Dimension - Length Side B inch	6.08 in
Dimension - Diameter Min Size inch	2.03 in
Dimension - N inch	0.50 in
Dimension - Bolt Size inch	0.38
Dimension - Length Overall inch	6.09 in

General

Trade Name	HYLUG™
Die Index	L115
Feature - Barrel Type	Long
Feature - Barrel Style	Chamfered
Plated	Y
Color Code	Yellow
Sub Brand	HYLUG
UPC	781810166178
Type	YAZ-2-NTFX, Long Barrel
	Narrow Tongue
Material	Copper
Plating Type	Tin - Electro Plated

Finish Type	Tin-Plated
UPC 14 Digit GTIN	00781810166178

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1800
Carton Quantity	25

Product Assets

- [Catalog \[English\]](#)
- [Installation Manual \[English\]](#)
- [Installation Manual \[French, English\]](#)



A Hubbell brand