



YAZ442TC38FX, Compression Terminal, 777.7 kcmil 1925/24 DLO, 750 kcmil Flex, 2- Hole, 3/8" Stud, 1" Spacing, Long Barrel

By Burndy

Catalog # [YAZ442TC38FX](#)

Copper Compression Terminal

Features

- Barrel is designed with an internal chamfer at the wire entry to ensure smooth insertion of the wire, preventing possible damaging of the strands
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Wire Size	750 KCMIL
Conductor - Copper Flex K Size	750
Conductor - Copper Flex M Size	750
Conductor - Copper Str Size	750 KCMIL
Conductor - Copper Flex I Size	750 kcmil
Range	
Conductor - Copper Flex G Size	750 KCMIL
Conductor - Copper DLO Size	777 kcmil
Range	
Conductor - Copper DLO Size	777 KCMIL
Conductor Size	750 KCMIL
Conductor - Copper Flex H Size	750 KCMIL
Conductor - Copper Flex G Size	750 kcmil
Range	
Conductor Type	FLEX
Conductor - Copper Str Size	750 kcmil
Range	



Conductor - Copper Flex H Size	750 kcmil
Range	
Conductor - Copper Flex I Size	750 KCMIL

Configuration

Physical Attribute - Number of Holes	2
Number of Pad Holes	2
Connector Type	LONG BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	2.19 in
Package Height	0.000 in
Dimension - Hole Size fraction	3/8
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	155 mm
mm	
Dimension - Outside Diameter	1.50 in
inch	
Dimension - Hole Size mm	10.4 mm
Dimension - Hole Size inch	0.41
Dimension - Strip Length inch	3-1/16
Dimension - Stud Size fraction	3/8
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Physical Attribute - Tongue	Straight
Angle	
Dimension - B Length fraction	3 in
Dimension - Z inch	0.53 in
Dimension - B Length inch	3.00 in
Dimension - N inch	0.50 in
Dimension - Bolt Size inch	0.38
Dimension - Length Overall	6.09 in
inch	

General

Trade Name	HYLUG™
Die Index	L115
Feature - Barrel Type	Long

Feature - Barrel Style	Skived	UPC 14 Digit GTIN	00781810135402
Plated	Yes		
Color Code	Yellow	Logistics	
Sub Brand	HYLUG	Minimum Pack Quantity	1
UPC	781810135402	Pallet Quantity	1392
Type	Long Barrel, Skive	Carton Quantity	6
Material	Copper		
Plating Type	Tin-Electro plated	Product Assets	
Finish Type	Tin-Plated	Catalog [English]	
UPC 12 Digit	781810135402		



A Hubbell brand