



YAZ4C2TC10E290, Compression Terminal, 4 AWG Cu, 2-Hole, #10 Stud, 3/4" Spacing, Long Barrel, 90 Degree

By Burndy

Catalog # [YAZ4C2TC10E290](#)

4 AWG, CU, 2 Hole, #10 Stud, 3/4 IN Spacing, Long Barrel,
Inspection Window, 90 Degree

Features

- Barrel is designed with an internal chamfer at the wire entry to ensure smooth insertion of the wire, preventing possible damaging of the strands
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding

Application

Wire Termination

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor Size	4 AWG
Conductor - Copper Str Navy Size	40 (19) Navy
Conductor - Material	COPPER
Conductor Type	CODE
Conductor - Copper Str Size	4 AWG

Configuration

Physical Attribute - Number of Holes	2
Number of Pad Holes	2
Connector Type	LONG BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	0.50 in
Dimension - Bolt Hole Size inch	0.20 in



Package Height	0.000 in
Dimension - Hole Size fraction	#10
Dimension - Bolt Size fraction	#8-#10
Physical Attribute - Tongue Angle	90 Degree
Dimension - Height inch	1.53 in
Angle - Pad	90 °
Dimension - B Length fraction	1-1/8 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Z inch	0.27 in
Dimension - L Length Overall	39 mm
Dimension - B Length inch	1.12 in
Dimension - Outside Diameter	0.34 in
inch	
Dimension - N inch	0.25 in
Dimension - Hole Size mm	5.3 mm
Dimension - Bolt Size inch	0.21
Dimension - Hole Size inch	0.21
Dimension - Length Overall	1.54 in
inch	
Dimension - Strip Length inch	1-3/16
Dimension - Stud Size fraction	#10

General

Feature - Barrel Type	Long
Feature - Barrel Style	Skived
Plated	Y
Color Code	Gray
Trade Name	HYLUG™
Physical Attribute - Tongue Type	Standard
Die Index	8
UPC	781810229057
Type	Long Barrel, Skive, Tin Plated
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810229057
UPC 14 Digit GTIN	00781810229057

Logistics

Minimum Pack Quantity	1
-----------------------	---



A Hubbell brand