



**YAZ6CTC1245, Compression Terminal, 6
AWG Cu, 1-Hole, 1/2" Stud, Long Barrel, 45
Degree**

By Burndy

Catalog # [YAZ6CTC1245](#)

6 AWG, CU, 1 Hole, 1/2 Stud, Long Barrel, Inspection Window, 45
Degree



Features

- Barrel is designed with an internal chamfer at the wire entry to ensure smooth insertion of the wire, preventing possible damaging of the strands
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding

Application

Wire Termination

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor Size	6 AWG
Conductor - Copper Str Navy Size	30 (19) Navy
Conductor - Material	COPPER
Conductor Type	CODE
Conductor - Copper Str Size	6 AWG

Configuration

Physical Attribute - Number of Holes	1
Number of Pad Holes	1
Connector Type	LONG BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	0.75 in
----------------------------	---------



A Hubbell brand

Dimension - Bolt Hole Size inch	0.52 in
Dimension - Hole Size fraction	1/2
Dimension - Bolt Size fraction	1/2
Physical Attribute - Tongue Angle	45 Degree
Dimension - Height inch	1.20 in
Angle - Pad	45 °
Dimension - B Length fraction	1-1/8 in
Dimension - Z inch	0.55 in
Dimension - L Length Overall mm	59 mm
Dimension - B Length inch	1.12 in
Dimension - Outside Diameter inch	0.29 in
Dimension - N inch	0.53 in
Dimension - Hole Size mm	13.5 mm
Dimension - Bolt Size inch	0.5
Dimension - Hole Size inch	0.53
Dimension - Length Overall inch	2.34 in
Dimension - Strip Length inch	1-3/16
Dimension - Stud Size fraction	1/2

General

Feature - Barrel Type	Long
Feature - Barrel Style Plated	Skived Y
Color Code	Blue
Trade Name	HYLUG™
Die Index	7
UPC	781810239421
Type	Long Barrel, Skive, Tin Plated
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810239421
UPC 14 Digit GTIN	00781810239421

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalog \[English\]](#)