



YAZ8C2TC1045, Compression Terminal, 8 AWG Cu, 2-Hole, #10 Stud, 5/8" Spacing, Long Barrel, 45 Degree

By Burndy

Catalog # [YAZ8C2TC1045](#)

8 AWG, CU, 2 Hole, #10 Stud, 5/8 IN Spacing, Long Barrel, Inspection Window, 45 Degree



Features

- Barrel is designed with an internal chamfer at the wire entry to ensure smooth insertion of the wire, preventing possible damaging of the strands
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Certification - cULus	No
EU RoHS Indicator	Contact Manufacturer
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Conductor - Copper Str Size	8 AWG
Conductor Size	8 AWG
Conductor - Copper Str Navy Size	23 (7) Navy
Conductor Type	CODE

Configuration

Physical Attribute - Number of Holes	2
Number of Pad Holes	2
Connector Type	LONG BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	0.41 in
----------------------------	---------

Package Height	0.000 in
Dimension - Hole Size fraction	#10
Dimension - Height inch	0.91 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	51 mm
Dimension - Outside Diameter inch	0.27 in
Dimension - Hole Size mm	5.3 mm
Dimension - Hole Size inch	0.21
Dimension - Strip Length inch	7/8
Dimension - Stud Size fraction	#10
Dimension - Bolt Hole Size inch	0.20 in
Dimension - Bolt Size fraction	#8-#10
Physical Attribute - Tongue Angle	45 Degree
Angle - Pad	45 °
Dimension - B Length fraction	3/4 in
Dimension - Z inch	0.28 in
Dimension - B Length inch	0.75 in
Dimension - N inch	0.25 in
Dimension - Bolt Size inch	0.21
Dimension - Length Overall inch	2.00 in

General

Trade Name	HYLUG™
Die Index	49
Feature - Barrel Type	Long
Feature - Barrel Style	Skived
Plated	Y
Color Code	Red
Physical Attribute - Tongue Type	Standard
UPC	781810196977
Type	Long Barrel, Skive, Tin Plated
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810196977
UPC 14 Digit GTIN	00781810196977

Logistics

Minimum Pack Quantity	100
Pallet Quantity	96000
Carton Quantity	100

Product Assets

[Catalog \[English\]](#)



A Hubbell brand