



YAZV102TC14SL, Compression Terminal, 14-10 AWG Cu, 2-Hole, 1/4" Stud, 3/4" Spacing, Long Barrel, Slotted

By Burndy

Catalog # [YAZV102TC14SL](#)

14-10 AWG, CU, 2 Hole, 1/4 Stud, 3/4 IN Spacing, Long Barrel, Inspection Window



Features

- Barrel is designed with an internal chamfer at the wire entry to ensure smooth insertion of the wire, preventing possible damaging of the strands
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding

Application

Wire Termination

Specifications

Standards - RoHS Compliance Status	CM
Industry Standard(s)	UL 486A-486B
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor Size	14-10 AWG
Conductor - Material	COPPER
Conductor Type	CODE
Conductor - Copper Str Size	14 AWG-10 AWG

Configuration

Physical Attribute - Number of Holes	2
Number of Pad Holes	2
Connector Type	LONG BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	0.41 in
Dimension - Bolt Hole Size inch	0.27 in
Package Height	0.000 in
Dimension - Hole Size fraction	1/4
Dimension - Bolt Size fraction	1/4
Length	2.28 in

Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	11/16 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Z inch	0.33 in
Dimension - L Length Overall mm	58 mm
Dimension - B Length inch	0.69 in
Dimension - Outside Diameter inch	0.21 in
Height	0.05 in
Width	0.41 in
Dimension - N inch	0.31 in
Dimension - Hole Size mm	6.9 mm
Dimension - Bolt Size inch	0.25
Dimension - Hole Size inch	0.27
Dimension - Length Overall inch	2.28 in
Dimension - Strip Length inch	3/4
Dimension - Stud Size inch	1/4
Dimension - Stud Size fraction	1/4
Dimensions	2.28 in x 0.41 in x 0.05 in

General

Feature - Barrel Type	Long
Feature - Barrel Style	• Chamfered • Skived
Plated	Y
Trade Name	HYLUG™
UPC	781810295212
Type	Long Barrel, Skive, Tin Plated
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810295212
UPC 14 Digit GTIN	00781810295212

Logistics

Minimum Pack Quantity	50
Carton Quantity	50

Product Assets

[Catalog \[English\]](#)

