



YAZV1C2TC14E2FX, Compression Terminal, 1 Flex G,H,I,K,M, DLO, 1 AWG B/C Cu, 2- Hole, 1/4" Stud, 3/4" Spacing, Long Barrel

By Burndy

Catalog # [YAZV1C2TC14E2FX](#)

1 Flex G,H,I,K,M,DLO, 1 AWG (B/C), CU, 2 Hole, 1/4 Stud, 3/4 IN
Spacing, Long Barrel, Inspection Window

Features

- Barrel is designed with an internal chamfer at the wire entry to ensure smooth insertion of the wire, preventing possible damaging of the strands
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Wire Size	1 AWG
Conductor - Copper Flex K Size	1 AWG
Range	
Conductor - Copper Flex K Size	"1 AWG"
Conductor - Copper Flex M Size	"1 AWG"
Conductor - Copper Str Size	"1 AWG"
Conductor - Copper Flex I Size	1 AWG
Range	
Conductor - Copper Flex G Size	"1 AWG"
Conductor - Copper DLO Size	1 AWG
Range	
Conductor - Copper Str	"1 AWG"
Compact Size	
Conductor - Copper DLO Size	1 AWG
Conductor Size	1 AWG
Conductor - Copper Flex H Size	"1 AWG"
Conductor - Copper Flex G Size	1 AWG
Range	
Conductor - Copper Str Navy	75
Size	



Conductor - CopperWeld Str Size	• 1 F AWG • 1 G AWG • 1 J AWG • 1 K AWG • 1 N AWG
Conductor Type	CODE/FLEX
Conductor - Copper Str Size	1 AWG
Range	
Conductor - Copper Flex H Size	1 AWG
Range	
Conductor - Copper Flex I Size	"1 AWG"

Configuration

Physical Attribute - Number of Holes	2
Number of Pad Holes	2
Connector Type	LONG BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	0.75 in
Package Height	0.000 in
Dimension - Hole Size fraction	1/4
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	80 mm
mm	
Dimension - Outside Diameter	0.51 in
inch	
Dimension - Hole Size mm	6.9 mm
Dimension - Hole Size inch	0.27
Dimension - Strip Length inch	1-7/16
Dimension - Stud Size fraction	1/4
Dimension - Bolt Hole Size inch	0.27 in
Dimension - Bolt Size fraction	1/4
Physical Attribute - Tongue	Straight
Angle	
Dimension - B Length fraction	1-3/8 in
Dimension - Z inch	0.34 in
Dimension - B Length inch	1.38 in
Dimension - Length Side B inch	3.16 in

Dimension - N inch	0.31 in	Plating Type	Tin
Dimension - Bolt Size inch	0.25	Finish Type	Tin-Plated
Dimension - Length Overall inch	3.16 in	UPC 12 Digit	781810228357
		UPC 14 Digit GTIN	00781810228357
General		Logistics	
Trade Name	HYLUG™	Minimum Pack Quantity	50
Die Index	11	Pallet Quantity	23200
Feature - Barrel Type	Long	Carton Quantity	50
Feature - Barrel Style	Skived		
Plated	Y	Product Assets	
Color Code	Green	Catalog [English]	
UPC	781810228357	Installation Manual [English]	
Type	Long Barrel, Skive	Installation Manual [French, English]	
Material	Copper		



A Hubbell brand