



YAZV252TC14FX, Cu Compression, 2-Hole, 1/4" Stud, 5/8" Spacing, Long Barrel, 1/0 Flex G, H, I, K, M, DLO, 1/0 AWG B, C

By Burndy

Catalog # [YAZV252TC14FX](#)

1/0 Flex G,H,I,K,M,DLO, 1/0 AWG (B/C), CU, 2 Hole, 1/4 Stud, 5/8 IN Spacing, Long Barrel, Inspection Window

Features

- Barrel is designed with an internal chamfer at the wire entry to ensure smooth insertion of the wire, preventing possible damaging of the strands
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Yes
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Wire Size	1/0 AWG
Conductor - Copper Flex K Size	1/0 AWG
Range	
Conductor - Copper Flex K Size	"1/0 AWG"
Conductor - Copper Flex M Size	"1/0 AWG"
Conductor - Copper Str Size	"1/0 AWG"
Conductor - Copper Flex I Size	1/0 AWG
Range	
Conductor - Copper Flex G Size	"1/0 AWG"
Conductor - Copper DLO Size	1/0 AWG
Range	
Conductor - Copper Str	"1/0 AWG"
Compact Size	
Conductor - Copper DLO Size	1/0 AWG
Conductor Size	1/0 AWG
Conductor - Copper Flex H Size	"1/0 AWG"
Conductor - Copper Flex G Size	1/0 AWG
Range	



Conductor - Copper Str Navy Size	100
Conductor - CopperWeld Str Size	• 1/0 F AWG • 1/0 G AWG • 1/0 J AWG • 1/0 K AWG
Conductor Type	CODE/FLEX
Conductor - Copper Str Size Range	1/0 AWG
Conductor - Copper Flex H Size Range	1/0 AWG
Conductor - Copper Flex I Size	"1/0 AWG"

Configuration

Physical Attribute - Number of Holes	2
Number of Pad Holes	2
Connector Type	LONG BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	0.83 in
Package Height	0.000 in
Dimension - Hole Size fraction	1/4
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	81 mm
Dimension - Outside Diameter inch	0.56 in
Dimension - Hole Size mm	6.9 mm
Dimension - Hole Size inch	0.27
Dimension - Strip Length inch	1-9/16
Dimension - Stud Size fraction	1/4
Dimension - Bolt Hole Size inch	0.27 in
Dimension - Bolt Size fraction	1/4
Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	1-1/2 in
Dimension - Z inch	0.34 in
Dimension - B Length inch	1.50 in

Dimension - Length Side B inch 3.20 in
Dimension - N inch 0.31 in
Dimension - Bolt Size inch 0.25
Dimension - Length Overall inch 3.20 in

General

Trade Name HYLUG™
Die Index 12
Feature - Barrel Type Long
Feature - Barrel Style

- Chamfered
- Skived

Plated Y
Color Code Pink
Sub Brand HYLUG
UPC 781810228395

Type Long Barrel, Skive
Material Copper
Plating Type Tin
Finish Type Tin-Plated
UPC 12 Digit 781810228395
UPC 14 Digit GTIN 00781810228395

Logistics

Minimum Pack Quantity 1
Pallet Quantity 23200
Carton Quantity 50

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[English\]](#)
[Installation Manual \[French, English\]](#)



A Hubbell brand