



YAZV25TC38FXB, Compression Terminal, 1/0 AWG, 1-Hole, 3/8" Stud, Long Barrel

By Burndy
Catalog # [YAZV25TC38FXB](#)

Copper Compression Terminal



Features

- Barrel is designed with an internal chamfer at the wire entry to ensure smooth insertion of the wire, preventing possible damaging of the strands
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Wire Size	1/0 AWG
Conductor - Copper Flex K Size	1/0 AWG
Range	
Conductor - Copper Flex K Size	"1/0 AWG"
Conductor - Copper Flex M Size	"1/0 AWG"
Conductor - Copper Str Size	"1/0 AWG"
Conductor - Copper Flex I Size	1/0 AWG
Range	
Conductor - Copper Flex G Size	"1/0 AWG"
Conductor - Copper DLO Size	1/0 AWG
Range	
Conductor - Copper Str	"1/0 AWG"
Compact Size	
Conductor - Copper DLO Size	1/0 AWG
Conductor Size	1/0 AWG
Conductor - Copper Flex H Size	"1/0 AWG"
Conductor - Copper Flex G Size	1/0 AWG
Range	
Conductor - Copper Str Navy	100
Size	
Conductor Type	CODE/FLEX

Conductor - Copper Str Size	1/0 AWG
Range	
Conductor - Copper Flex H Size	1/0 AWG
Range	
Conductor - Copper Flex I Size	"1/0 AWG"

Configuration

Physical Attribute - Number of Holes	1
Number of Pad Holes	1
Connector Type	LONG BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	0.83 in
Package Height	0.000 in
Dimension - Hole Size fraction	3/8
Package Weight	0.000 lb.
Package Length	0.000 in
Outside Diameter	0.56 in
Package Width	0.000 in
Dimension - L Length Overall mm	70 mm
Dimension - Outside Diameter inch	0.56 in
Weight	0.077 lb.
Width	0.83 in
Dimension - Hole Size mm	10.4 mm
Dimension - Hole Size inch	0.41
Dimension - Stud Size fraction	3/8
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Length	2.75 in
Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	1-1/2 in
Dimension - Z inch	0.42 in
Dimension - B Length inch	1.50 in
Dimension - N inch	0.41 in
Dimension - Inside Diameter inch	0.44 in
Dimension - Bolt Size inch	0.38

Dimension - Length Overall inch	2.75 in	Material	Copper
		Plating Type	Tin - Electro Plated
		Finish Type	Tin-Plated
		UPC 12 Digit	781810431276
		UPC 14 Digit GTIN	00781810431276
General		Logistics	
Trade Name	HYLUG™	Minimum Pack Quantity	50
Die Index	12	Pallet Quantity	23200
Feature - Barrel Type	Long	Carton Quantity	50
Feature - Barrel Style	- Belled - Skived		
Plated	Y		
Color Code	Pink		
UPC	781810431276		
Type	Long Barrel, Skive	Product Assets	
		Catalog [English]	



A Hubbell brand